



PIP® Traverse™ FB

Full Brim, Non-Vented, Industrial Climbing Helmet with Mips® Brain Protection System for Industrial Safety Helmets, ABS Shell with Quin® Tag, EPS Foam Impact Liner, HDPE Suspension, Wheel Ratchet Adjustment and 4-Point Chin Strap

- Ultra lightweight full brim shell made with ABS material provides superior protection
- Mips® (Multi-directional Impact Protection System) Brain Protection System for Industrial Safety Helmets is a low frictional layer designed to reduce rotational motion transferred to the head from angled impacts
- Pre-installed Quin® Tag enables you to digitally store critical medical ID and other essential info to be scanned in the event of an emergency
- EPS foam impact liner helps absorb the forces of front, side, or rear impacts
- Includes a 4-point cross-over chin strap with quick release buckle that is adjustable for a safe & secure fit
- Rugged non-slip adjustable SURE-LOCK wheel ratchet ensures proper suspension performance and effortless fit for all head sizes



Technical Data

Color	Hi-Vis Yellow, Brown Carbon, Black, Black Carbon, White, Red, Yellow, Dark Green, White Carbon, Navy, Orange, Gray
Sizes Available	OS
Packaging	Boxed
Packed	6/Case
Case Dimensions (in)	22.44 x 13.78 x 14.57
Case Weight (lbs)	13.89
Country of Origin	China
Shell Material	ABS
Shell	Non-Vented
Brim Style	Full
Size Adjustment	Wheel Ratchet
Suspension	Foam Cradle System
Chin Strap	4-Point Polyester
Sweatband	Nylon Backed Foam
Size Range	53cm-63cm
Construction	MIPS Technology, Quin Intelligent Safety Technology
Certifications	ANSI/ISEA Z89.1, EN 12492

Performance Data

ANSI Type	Type II
Electrical Class	Class E

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP1491RM-FB-11	Black	OS	198987042783	10198987042780	20198987042787
280-HP1491RM-FB-30	Black Carbon	OS	198987041410	10198987041417	20198987041414
280-HP1491RM-FB-50	Brown Carbon	OS	198987058227	10198987058224	20198987058221
280-HP1491RM-FB-04	Dark Green	OS	198987042790	10198987042797	20198987042794
280-HP1491RM-FB-09	Gray	OS	198987041175	10198987041172	20198987041179
280-HP1491RM-FB-44	Hi-Vis Yellow	OS	198987041182	10198987041189	20198987041186
280-HP1491RM-FB-08	Navy	OS	198987041199	10198987041196	20198987041193
280-HP1491RM-FB-03	Orange	OS	198987041205	10198987041202	20198987041209
280-HP1491RM-FB-15	Red	OS	198987041212	10198987041219	20198987041216
280-HP1491RM-FB-01	White	OS	198987041229	10198987041226	20198987041223
280-HP1491RM-FB-40	White Carbon	OS	198987041427	10198987041424	20198987041421
280-HP1491RM-FB-02	Yellow	OS	198987041236	10198987041233	20198987041230