



P65

Technical Data



Color	Dark Blue
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	23.46 x 13.94 x 16.34
Case Weight (lbs)	15.43
Country of Origin	Taiwan
Lens	Clear
Frame Style	Semi-Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	FogLess 3Sixty, Anti-Scratch
Bridge	Rubber
Temple	Molded
Base Curve	8.5
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Bouton® Optical Xtricate™ Semi-Rimless Safety Glasses with Dark Blue Frame, Clear Lens and FogLess® 3Sixty™ Coating

- Rubber nose pads offer a more secure fit
- Lightweight, semi-rimless design provides all day user comfort
- Flexible temples provide a secure fit without uncomfortable pressure points
- FogLess® 3Sixty™ enhanced hydrophobic action resists lens fogging and provides clear vision in extreme working conditions
- 8.5 Base curve lens
- Meets ANSI Z87.1-2015 standards
- **⚠ WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-13

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-59-0520	Dark Blue	Clear	Clear	FL360/AS	616314267246	01616314267245	02616314267244
250-59-0521	Dark Blue	Tinted	Green	FL360/AS	616314267253	01616314267252	02616314267251
250-59-0551	Dark Blue	Tinted	Light Gray	FL360/AS	616314267260	01616314267269	02616314267268

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated