


EMT One Hole Straps

Size Range: 1/2" - 4"
 Product Series: CSE - 1 Hole EMT Strap
 Material: Steel Construction
 Bright Electro Zinc Plated
 Made in the USA

Industrial SPEC-grade

CSE Series Steel EMT Straps

AMFICO Steel One Hole Straps Snap On to the Conduit Allowing the Installer to Easily Position the Strap Prior to Mounting. Alignment of EMT is Quick and Easy.



Cat #	TRADE SIZE	A LENGTH	B HEIGHT	C HOLE ID	Unit Ctn.	Mstr. Ctn.	Wt. Per/C
CSE501	1/2"	1-5/8"	11/16"	1/4"	100	1000	3
CSE751	3/4"	1-7/8"	15/16"	1/4"	100	500	4
CSE1001	1"	2-1/8"	1-3/16"	5/16"	50	250	6
CSE1251	1-1/4"	2-3/4"	1-1/2"	3/8"	30	150	9
CSE1501	1-1/2"	3"	1-3/4"	3/8"	25	125	13
CSE2001	2"	3-3/4"	2-3/16"	7/16"	20	100	17
CSER2501	2-1/2"	4-3/4"	2-7/8"	9/16"	-	20	42
CSER3001	3"	5-3/8"	3-1/2"	9/16"	-	10	49
CSER3501	3-1/2"	6"	4"	9/16"	-	10	71
CSER4001	4"	6-1/2"	4-1/2"	9/16"	-	10	78

Compliances:
 Certified Made in the USA
 Indoor or Outdoor Use
 RoHS Compliant
 REACH Compliant
 CA Prop 65 Compliant
 UNSPSC 31162310



Available OPTIONS:

2 Hole Straps EMT and Rigid

One-Hole BX Type

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
CSBX381	12-2, 12-3, 10-2, 10-3	100	1000	1

Industrial Electrical Fittings SPECgrade Hardware & Accessories

*The Perfect Compliment for Our Fittings and
Your Installations*

Hangers
Straps
Locknuts
Penetration Sleeves
Hardware

Hardware & Accessories 2020



**Products You Can Trust
Integrity You Can Count On**

EMT One Hole Straps

Size Range: 1/2" - 4"

Product Series: CSE - 1 Hole EMT Strap

Material: Steel Construction


Bright Electro Zinc Plated

Made in the USA

Industrial SPEC-grade

CSE Series Steel EMT Straps

AMFICO Steel One Hole Straps Snap On to the Conduit Allowing the Installer to Easily Position the Strap Prior to Mounting. Alignment of EMT is Quick and Easy.



Cat #	TRADE SIZE	A LENGTH	B HEIGHT	C HOLE ID	Unit Ctn.	Mstr. Ctn.	Wt. Per/C
CSE501	1/2"	1-5/8"	11/16"	1/4"	100	1000	3
CSE751	3/4"	1-7/8"	15/16"	1/4"	100	500	4
CSE1001	1"	2-1/8"	1-3/16"	5/16"	50	250	6
CSE1251	1-1/4"	2-3/4"	1-1/2"	3/8"	30	150	9
CSE1501	1-1/2"	3"	1-3/4"	3/8"	25	125	13
CSE2001	2"	3-3/4"	2-3/16"	7/16"	20	100	17
CSER2501	2-1/2"	4-3/4"	2-7/8"	9/16"	-	20	42
CSER3001	3"	5-3/8"	3-1/2"	9/16"	-	10	49
CSER3501	3-1/2"	6"	4"	9/16"	-	10	71
CSER4001	4"	6-1/2"	4-1/2"	9/16"	-	10	78

Compliances:

Certified Made in the USA
 Indoor or Outdoor Use
 RoHS Compliant
 REACH Compliant
 CA Prop 65 Compliant
 UNSPSC 31162310



Available OPTIONS:

2 Hole Straps EMT and Rigid

One-Hole BX Type

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
CSBX381	12-2, 12-3, 10-2, 10-3	100	1000	1