



PIP® Whistler™

Cap Style, HDPE Shell, 4-Point Textile Suspension, Ratchet Adjustment

- Lightweight shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- Shell design includes a rain trough for extra convenience in adverse weather conditions
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments
- Precise height adjustment settings to ensure proper depth

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	Sky Blue, Beige, Gold, Black, Yellow, Hi-Vis Red, Royal, Lime, Hi-Vis Orange, Dark Gray, Forest Green, Orange, Red, Navy, Light Blue, Dark Green, Hi-Vis Yellow, Gray, Brown, White, Pink, Northern Blue
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	20.30 x 14.00 x 28.10
Case Weight (lbs)	14.55
Country of Origin	Canada
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP241R-10	Beige	OS	620606000244	10616314393058	10620606000241
280-HP241R-11	Black	OS	620606000251	10616314306256	10620606000258
280-HP241R-12	Brown	OS	620606000268	10616314312363	10620606000265
280-HP241R-14	Dark Gray	OS	6206060005270	106206060005277	106206060005277
280-HP241R-04	Dark Green	OS	6206060000183	106206060000180	106206060000180
280-HP241R-74	Forest Green	OS	620606189741	10616314817196	10620606189748
280-HP241R-13	Gold	OS	6206060002415	10616314398886	106206060002412
280-HP241R-09	Gray	OS	620606000237	10620606000234	10620606000234
280-HP241R-31	Hi-Vis Orange	OS	6206060002187	106206060002184	106206060002184
280-HP241R-05	Hi-Vis Red	OS	6206060000190	10616314415088	106206060000197
280-HP241R-44	Hi-Vis Yellow	OS	6206060002194	106206060002191	106206060002191
280-HP241R-06	Light Blue	OS	620606000206	10616314366205	10620606000203
280-HP241R-45	Lime	OS	6206060004105	106206060004102	106206060004102
280-HP241R-08	Navy	OS	620606000220	10616314366366	10620606000227
280-HP241R-18	Northern Blue	OS	6206060004679	106206060004676	106206060004676
280-HP241R-03	Orange	OS	6206060000176	106206060000174	106206060000173
280-HP241R-20	Pink	OS	6206060002170	106206060002177	106206060002177
280-HP241R-15	Red	OS	6206060000275	106206060000273	106206060000272
280-HP241R-17	Royal	OS	6206060000282	10616314313360	106206060000289
280-HP241R-07	Sky Blue	OS	6206060000213	106206060000210	106206060000210
280-HP241R-01	White	OS	6206060000152	106206060000159	106206060000159
280-HP241R-02	Yellow	OS	6206060000169	106206060000166	106206060000166