



A200 AC Coil, 110/120V, 60 Hz, Size 6

A200 AC Coil, 120/110V, 60/50 Hz,
Two-, Three-Pole, Sizes 3 and 4, Model JDC Coils ^①

Voltage	Size 0	Size 1	Size 2
	Single-, Two-, Three-, Four-Pole	Single-, Two-, Three-, Four-Pole	Single-, Two-, Three-, Four-Pole
12	1268C86G07	1268C86G07	1268C86G07
24	1268C86G04	1268C86G04	1268C86G04
48	1268C86G05	1268C86G05	1268C86G05
125	1268C86G02	1268C86G02	1268C86G02
250	1268C86G01	1268C86G01	1268C86G01
125/250 ^②	1268C86G03	1268C86G03	1268C86G03

Kits for Model J-K, Sizes 3 and 4 ^③

Description	Poles	Size 3—Model J	Size 4—Model J	Size 4—Model K ^④
Contact kit	2	626B187G12	626B187G16	5250C81G16
	3	626B187G13	626B187G17	5250C81G17
	4	626B187G14 ^⑤	626B187G18 ^⑦	5250C81G18
	5	626B187G15 ^⑤	626B187G19 ^⑤	5250C81G19
Arc box	2-3	6714C74G09	6714C74G11	6714C74G11
	4-5	6714C74G10	6714C74G12	6714C74G12
Cross bar	2-3	672B788G36	672B788G36	672B788G40
	4-5	672B788G38	672B788G38	—
Upper base	2-3	672B788G37	672B788G37	672B788G52
	4-5	672B788G39	672B788G39	—
Lower base	2-3	1250C33G03	1250C33G03	1250C33G10
	4-5	1250C33G06	1250C33G06	—
KO spring (pk. of 10)	All	503C796G02	503C796G02	672B788G50
Terminals line/load (pk. of 3)	All	372B357G12	372B357G13	372B357G13

AC Coils

Voltage	Hz	Model J, Sizes 3-4		Model K, Size 4 ^⑥	
		Two-, Three-Pole	Four-, Five-Pole	Two-, Three-Pole	Four-, Five-Pole
120/110	60/50	505C633G01	505C635G01	5250C79G01	5250C80G01
208	60	505C633G02	505C635G02	5250C79G02	5250C80G02
600/550	60/50	505C633G05	505C635G05	5250C79G05	5250C80G05
380	50	505C633G07	505C635G07	5250C79G07	5250C80G07
240/220	60/50	505C633G12	505C635G12	5250C79G12	5250C80G12
480/440	60/50	505C633G13	505C635G13	5250C79G13	5250C80G13
24	60	505C633G34	N/A	5250C79G34	N/A
277	60	505C633G14	N/A	5250C79G14	N/A
240/480 ^⑧	60/60	505C633G03	505C635G03	5250C79G03	5250C80G03
120/240 ^⑧	60/60	505C633G10	505C635G10	5250C79G10	5250C80G10

DC Coils ^⑨

Voltage	Model J, Sizes 3-4
	Two-, Three-Pole
24	1255C68G04
48	1255C68G05
125	1255C68G01
250	1255C68G02
125/250	1255C68G03

Notes

- ^① Use only on contactors originally supplied with a DC coil.
- ^② Dual voltage coils. Use only on contactors or starters originally supplied with a dual voltage coil.
- ^③ Model C contact kits and coils 00-4, two-, three-, four- and five-pole contactors are same as Model J. All other parts are unavailable.
- ^④ Model K replaces Model J.
- ^⑤ Use quantity two—626B187G12 (two-pole kits).
- ^⑥ Use one of each of 626B187G12 (two-pole kit) and 626B187G13 (three-pole kit).
- ^⑦ Use quantity two—626B187G16 (two-pole kit).
- ^⑧ Use one each of 626B187G16 (two-pole kit) and 626B187G17 (three-pole kit).
- ^⑨ Model K replaces Model J.
- ^⑩ Dual voltage coils. Use only on contactors or starters originally supplied with a dual voltage coil.
- ^⑪ Use only on units originally supplied with DC coil.

120V Coil for Electrically Held Lighting Contactor—Style Number 505C633G01



AC Coils Electrically Held

Voltage	Hz	30A		60A	
		Two-, Three-, Four-Pole	Five-Pole	Two-, Three-Pole	Four-, Five-Pole
120/110	60/50	505C806G01	505C808G01	505C806G01	505C818G01
208	60	505C806G02	505C808G02	505C806G02	505C818G02
600/550	60/50	505C806G05	505C808G05	505C806G05	505C818G05
380	50	505C806G07	505C808G07	505C806G07	505C818G07
240/220	60/50	505C806G12	505C808G12	505C806G12	505C818G12
480/440	60/50	505C806G13	505C808G13	505C806G13	505C818G13
24	60	505C806G16	N/A	505C806G16	505C818G15
227	60	505C806G18	505C808G16	505C806G18	505C818G16
240/480 ①	60/60	505C806G03	505C808G03	505C806G03	505C818G03
120/240 ①	60/60	505C806G10	505C808G10	505C806G10	505C818G10

AC Coils Electrically Held, continued

Voltage	Hz	100 and 200A—Model J		200A—Model K ②	
		Two-, Three-Pole	Four-, Five-Pole	Two-, Three-Pole	Four-, Five-Pole
120/110	60/50	505C633G01	505C635G01	52050C79G01	5250C80G01
208	60	505C633G02	505C635G02	52050C79G02	5250C80G02
600/550	60/50	505C633G05	505C635G05	52050C79G05	5250C80G05
380	50	505C633G07	505C635G07	52050C79G07	5250C80G07
240/220	60/50	505C633G12	505C635G12	52050C79G12	5250C80G12
480/440	60/50	505C633G13	505C635G13	52050C79G13	5250C80G13
24	60	505C633G34	N/A	52050C79G34	N/A
227	60	505C633G14	N/A	52050C79G14	N/A
240/480 ①	60/60	505C633G03	505C635G03	52050C79G03	5250C80G03
120/244 ①	60/60	505C633G10	505C635G10	52050C79G10	5250C80G10

Notes

① Dual voltage coils. Use only on contactors or starters originally supplied with a dual voltage coil.

② Model K replaces Model J. Renewal parts are different. **Use parts for proper model only.**