



EAN: 4013288223043
Part number: 05075832001
Article number: Safe-Torque A 2 Set 1

Size: 275x100x65 mm
Weight: 1070 g
Country of origin: CZ
Customs tariff number: 82041100

- Slip-over release mechanism - the set torque can never be overtightened
- Torque Lock function: The torque function can be deactivated and the tool can then be used as a standard ratchet with high loosening moments and for applications with defined angles of rotation
- For controlled clockwise and counterclockwise torque operation - tightening and loosening with or without torque
- Easy setting and saving of the desired torque value with audible and tactile clicks when reaching the scale values
- After the target torque has been reached, the release angle is only 30°
- The fine toothing with 72 teeth allows for a low return angle of 5°
- 1/4" hexagon drive for the use of 1/4" bits
- Use of 1/4" sockets also possible with the Wera adaptor 870/1

23-piece set; in surface-friendly, compact and extremely robust textile box. Small size and low weight for better mobility. 1 Safe-Torque A 2 torque wrench with 1/4" hexagonal drive, measuring range 2-12 Nm; for controlled clockwise and counterclockwise torque operation; tightening and loosening with or without torque, disengageable torque function (Torque Lock function); 72 teeth; low return angle of 5°; easy setting and saving of the desired torque value, with audible and tactile locking when the scale values are reached, slip-over release mechanism when the set torque is reached; ergonomic 2-component handle; 9 Zyklop sockets, 12 bits (1/4", 50 mm long), one connector for sockets (1/4" external hexagon to 1/4" external square head).



Web link
<https://www.wera.de/en/05075832001>


Wera - Safe-Torque A 2 Set 1
05075832001 - 4013288223043

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de



Safe-Torque

Slide-over mechanism prevents application of excessive torques



The Safe-Torque A2 torque wrench is equipped with a slide-over mechanism. Once the set torque has been reached, the tool cannot be overtightened, so that excessive torque cannot be applied.

Torque Lock function



The torque function can be deactivated. The Safe-Torque torque wrench can then also be used as a standard ratchet with high loosening moments and for applications with defined angles of rotation.

For clockwise and counterclockwise operation



The Safe-Torque torque wrench is suitable for clockwise and counterclockwise operation with a set torque. When the Torque Lock function is deactivated, tightening and loosening is enabled without torque.

Easy torque setting




Easy setting and saving of the required torque with audible and tactile clicks on reaching the scale values.

Low return angle



The fine-toothed Safe-Torque torque wrench with 72 teeth has a back-pivoting angle of only 5°. The small stroke offers quick and precise working in all installation positions.

For 1/4" hex drive bits



The Safe-Torque A 2 torque wrench has a 1/4" bit mounting with a strong permanent magnet and is suitable for bits with 1/4" external hexagon drive as per DIN ISO 1173-C 6.3 and E 6.3 and Wera connection series 1 and 4.

Adapter for 1/4" sockets



With the 870/1 connector (1/4" external hexagon to 1/4" external square head) the Safe-Torque A 2 can also be used with 1/4" sockets.

Web link

<https://www.wera.de/en/05075832001>

Wera - Safe-Torque A 2 Set 1
05075832001 - 4013288223043

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

Safe-Torque A 2 torque wrench with 1/4" hexagon drive, 2-12 Nm, 2-12 Nm



05075801001

1x 2-12 Nm



8790 HMA Zyklus 1/4" socket, 5.5 x 23 mm



05003504001

1x 5.5 x 23 mm

05003505001

1x 6 x 23 mm

05003506001

1x 7 x 23 mm

05003507001

1x 8 x 23 mm

05003508001

1x 9 x 23 mm

05003509001

1x 10 x 23 mm

05003510001

1x 11 x 23 mm

05003511001

1x 12 x 23 mm

05003512001

1x 13 x 23 mm

870/1 Adaptor, 1/4" x 25 mm



05136000001¹⁾

1x 1/4" x 25 mm

1) With friction ball; for manual nut spinner sockets

851/4 Z bits, PH 2 x 50 mm



1x PH 2 x 50 mm

867/4 Z TORX® bits, TX 10 x 50 mm



05060132001

1x TX 10 x 50 mm

05060133001

1x TX 15 x 50 mm

05060134001

1x TX 20 x 50 mm

05060135001

1x TX 25 x 50 mm

05060136001

1x TX 27 x 50 mm

05060137001

1x TX 30 x 50 mm

840/4 Z bits, 2.5 x 50 mm



05059604001

1x 2.5 x 50 mm

05059605001

1x 3 x 50 mm

05059610001

1x 4 x 50 mm

05059615001

1x 5 x 50 mm

05059620001¹⁾

1x 6 x 50 mm

1) Hexagonal blade

Hook and Loop Fastener Strip 240, 50 x 240 mm

1x 50 x 240 mm



Web link

<https://www.wera.de/en/05075832001>

Wera - Safe-Torque A 2 Set 1
05075832001 - 4013288223043

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de