

Apollo

Solar Flagpole Light



Illuminate your flag proudly with this easy-to-install flag pole light, featuring a wide 180° light coverage for excellent nighttime visibility. Equipped with 32 pieces of super bright white LEDs delivering 1260Lm, it provides powerful illumination for up to 12 hours after a full charge.

The light automatically switches on at dusk and off at dawn for hassle-free operation, and its IP65 rating ensures durable performance in all kinds of outdoor weather.

Specifications

Lumens..... 1260LM

Power32W

Solar Panel

Power5V, 6W *2

Li-ion battery

Capacity3.2V, 5000mAh LiFePO4 rechargeable battery * 2

LED

LED Qty 16pcs x 1W pure super bright white LEDs *2

CCT 6000K

Performance

Working Time..... Up to 12 hours


Switch.....Automatic on and off at dusk/dawn

IP Class IP65

Material..... PC+ABS+Aluminum bracket+Stainless steel hook

Model Number..... AVS-JY8-9009

SKU 990206



Beyond Solar retains the right to modify or change product specifications without prior notice, as part of our ongoing commitment to improvement.

Automatic on at dusk and off at dawn for hassle-free operation.




Beyond Solar retains the right to modify or change product specifications without prior notice, as part of our ongoing commitment to improvement.

Additional Features:


Beyond's Flagpole Light	Others Flagpole Light
 180° Complete coverage	 ≈120° incomplete
 32pcs Highlighting LED	 ≈16pcs Small light bulb
 19.3inch Large-panel fast charging	 ≈16inch Slow charging

Beyond Solar retains the right to modify or change product specifications without prior notice, as part of our ongoing commitment to improvement.


Installation Instructions




1
Turn on the switches on both sides



2
Install the connecting piece to the bottom of the body.



3
Fix the bracket onto the flagpole and tighten the screws.



4
Fix the fuselage to the support and complete the installation.

Beyond Solar retains the right to modify or change product specifications without prior notice, as part of our ongoing commitment to improvement.

Installation Instructions

Read and follow all instructions before applying your solar flagpole light. Please keep this instruction for further reference.

How to check ON/OFF status:

1. Cover the panel with thick cloth (to simulate darkness).
2. Press the ON/OFF button: lights on = ON; if off, press again.

No further action is needed once set to ON.

Troubleshooting

1. Check if the solar panel is shaded by trees or covered with dust.
2. Keep the panel away from other light sources.
3. Verify that the switch is turned on.
4. Replace the battery.
5. Contact us for further assistance.

CHARGE YOUR LIGHT for 8 HOURS AT LEAST BEFORE FIRST USE

(Put your solar panel exposed to the sunlight without shelter when charging)

Beyond Solar retains the right to modify or change product specifications without prior notice, as part of our ongoing commitment to improvement.

Product Components




A. Solar light 2 pcs
B. Hooks 2 pcs
C. Metal bracket 2 pcs

D. Connecting rod 2 pcs
E. Connecting head 2 pcs
F. Screwdriver 1 pc

Beyond Solar retains the right to modify or change product specifications without prior notice, as part of our ongoing commitment to improvement.

Dimensions



Fits 2-6 inch Flag Pole

*All Dimensions are in Inches (in)

Beyond Solar retains the right to modify or change product specifications without prior notice, as part of our ongoing commitment to improvement.

Apollo | Solar Flagpole Light



Beyond Solar retains the right to modify or change product specifications without prior notice, as part of our ongoing commitment to improvement.

Office: 1939 Parker Court,
Stone Mountain, GA 30087, U.S.A.

Phone:
1-800-316-4716

Email:
sales@beyondsolar.net

Website:
beyondsolar.net