



TEGERA® INFINITY 8800

Learn more

SOFT, SMOOTH FINISH, PALM DIPPED

Dexterous work glove, 15 gg knitted with nitrile foam palm dipping with smooth surface that provides excellent grip on dry and moist surfaces. Breathable materials for all day comfort. Protection against contact heat up to 100°C/212°F. Wide range of sizes means a perfectly fitting glove for everyone. Skin friendly with Derma-test and Oeko-Tex certificate.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Durable
- Good grip
- Extra comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs
- Thin

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping

PRIMARY ENVIRONMENTS OF USE

Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Machine operating, Installation work, HVAC installation, Engineering, Transport work, Machine driving, Warehouse work, Airport work, Repair work, Service work, Shop work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Facility management services, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Public safety, security and defence, Retail and wholesale, Transport equipment manufacturing, Transportation and logistics, Warehousing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Heat protection gloves, Precision work gloves
CATEGORY Cat. II
COLLECTION Infinity
KNITTING GAUGE (GG) 15
LINING MATERIAL Nylon, Spandex
LENGTH 205-265 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Nylon, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4121X

EN 407:2020 (No flame protection) X1XXXX

ANSI 3 ABR

Contact heat rating valid for palm area only

SIZE		ARTICLE NUMBER	EAN
5	XXS	8800-5	7340118327631
6	XS	8800-6	7340118318486
7	S	8800-7	7340118318493
8	M	8800-8	7340118318509
9	L	8800-9	7340118318516
10	XL	8800-10	7340118318462
11	XXL	8800-11	7340118318479

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.