

Steel square covers

COVERS FOR 4" SQUARE BOXES – CUBIC INCH CAPACITY (SEE BELOW)

UL LISTED


#8-32 screw used on covers




TP472



TP472RED



TP474



TP478
TP487



TP473, TP475, TP476,
TP477, TP479, TP483



TP850^B



TP854^B



AMR0

Cat. #	Description	Unit qty.	Wt. lbs. per 100	Capacity cu. in.
TP472 ^H	Flat blank	50	31	-
TP472RED	Flat blank, red	50	31	-
TP474 ^H	Flat, open with ears 2 ³ / ₄ "	50	21	-
TP478 ^H	Flat, with 1/2" KO	50	31	-
TP478RED ^H	Flat, with 1/2" KO	50	31	-
TP487 ^H	Flat, with 3/4" KO	50	29	-
TP473 ^H	Raised 1/4", open with ears 2 ³ / ₄ "	50	23	1.3
TP476 ^H	Raised 1/2", open with ears 2 ³ / ₄ "	50	26	4.0
TP477 ^H	Raised 5/8", open with ears 2 ³ / ₄ "	50	27	5.0
TP475 ^H	Raised 3/4", open with ears 2 ³ / ₄ "	25	31	6.0
TP479 ^H	Raised 1", open with ears 2 ³ / ₄ "	25	34	7.0
TP483 ^{C H}	Raised 1 1/4", open with ears 2 ³ / ₄ "	25	31	9.5
AMR0 ^I	3/4" - 1 1/2" round adjustable mud ring	25	44	6.1

Air Plenum

TP850 ^B	Flat blank gasketed with captive screws	25	31	-
TP854 ^B	Flat ring double gasketed	25	12	-

^B For air plenum (no mounting holes) - not UL Listed.

^C cUL Listed.

^I ETL listed.

^H CSA certified.

MUD RINGS FOR 4" SQUARE STEEL OUTLET BOXES

UL LISTED



TP480



TP482, TP484,
TP486, TP489



TP494



TP488, TP490



TP496



TP501, TP502



AMR1



AMR2



AMR158

Cat. #	Description	Unit qty.	Wt. lbs. per 100	Capacity cu. in.
One Device				
TP480 ^H	Flat	50	20	-
TP482 ^H	1/4" raised	50	21	1.8
TP484 ^H	1/2" raised	50	23	3.8
TP489 ^H	5/8" raised	50	26	4.3
TP489RED ^H	5/8" raised	50	26	4.3
TP486 ^H	3/4" raised	50	30	5.5
TP488 ^H	1" raised	50	34	6.8
TP490 ^H	1 1/4" raised	25	39	8.5
AMR1 ^C	3/4" - 1 1/2" raised adjustable	25	47	-
AMR158 ^C	5/8" - 1 1/4" raised adjustable	25	44	6.0
Two Device				
TP494 ^H	Flat	50	12	-
TP496 ^{H K}	1/4" raised	50	13	3.0
TP498 ^{H K}	1/2" raised	50	18	6.0
TP499 ^{H K}	5/8" raised	50	22	8.0
TP500 ^{H K}	3/4" raised	50	24	9.0
TP501 ^H	1 1/4" raised	25	31	14.0
TP502 ^H	1" raised	25	30	11.7
AMR2 ^C	5/8" - 1 1/2" raised adjustable	25	50	11.3

^C cUL Listed.

^H CSA certified.

^K Slotted design for use with 4" square box partitions.