



G-Tek® ECO Series™ Hi-Vis Seamless Knit Dyneema® Diamond 2.0 Blended Glove with Nitrile Coated Foam Grip on Palm & Fingers

- Seamless construction offers increased comfort and breathability
- Dyneema® Diamond 2.0/spandex shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Foam nitrile coatings are breathable and durable, designed with a cell structure that disperse fluids on contact for an improved grip
- Knit wrist helps prevent dirt and debris from entering the glove
- Hi-vis coloring makes this product very easy to see
- Color coded hems for easy size identification

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Medium to Large Parts and Materials
- Metal Fabrication
- Mechanical Equipment Maintenance and Repair
- Heavy to Medium Fastening and Anchoring



Technical Data

Color	Hi-Vis Orange
Sizes Available	XS-2XL
Packaging	Pair Bagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	11.81 x 12.60 x 15.75
Case Weight (lbs)	14.99
Country of Origin	China
Liner Material	Dyneema Diamond 2.0 Technology
Coating	Nitrile
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Foam
Gauge	13
Cuff	Knit Wrist
Construction	Coated Seamless Knit, Coreless Technology
Certifications	21 CFR
Product Circularity	Reusable / Launderable Contains Bio-Based Materials

Performance Data

Cut Level	A4
ANSI Abrasion Level	6
ANSI Puncture Level	4
EN 388	4X43DX

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
19-D340OR/XS	Hi-Vis Orange	XS	616314118746	01616314118745	02616314118744
19-D340OR/S	Hi-Vis Orange	S	616314118722	01616314118721	02616314118720
19-D340OR/M	Hi-Vis Orange	M	616314118715	01616314118714	02616314118713
19-D340OR/L	Hi-Vis Orange	L	616314118708	01616314118707	02616314118706
19-D340OR/XL	Hi-Vis Orange	XL	616314118739	01616314118738	02616314118737
19-D340OR/XXL	Hi-Vis Orange	2XL	616314118753	01616314118752	02616314118751