



**MCR  
SAFETY**

# 9673 Memphis Dipped Specification Sheet

## PRODUCT DESCRIPTION:

These styles are well suited for Multi-Industrial applications that require high dexterity and comfort. The 9673 features a seamless 13 gauge gray nylon shell and black nitrile foam dipped palm and fingers. This material is breathable and cool and offers comfort and grip.

## FEATURES:

- 13 Gauge Gray Nylon Shell
- Black Nitrile Foam Palm and Fingers
- Knit Wrist
- Cool and Comfortable
- Easy to wear

## APPLICATIONS:

Agriculture, Assembly Line Production, Automotive Assembly, Carpentry, Construction, Demolition, Furniture industry, Janitorial , Landscaping



## TECHNICAL DATA FOR: 9673

<b>Series</b>	Memphis	<b>EN 388: CE Score - Abrasion</b>	4
<b>Material Group</b>	Strings	<b>EN 388 : CE Score - Cut</b>	1
<b>Product Type</b>	Dipped	<b>EN 388 : CE Score - Tear</b>	2
<b>Glove Size</b>	Large	<b>EN 388 : CE Score - Puncture</b>	1
<b>Gauge</b>	13 Gauge	<b>ANSI Puncture</b>	2
<b>Material</b>	Nylon	<b>ANSI Abrasion</b>	3
<b>Made In</b>	China		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA


Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2021 MCR Safety - All Rights Reserved



**MCR**  
SAFETY

**9673**  
**Memphis**  
**Dipped**  
**Specification Sheet**



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9673XL	X - Large	10.70	4.25	2.90	16.464 lb.	1.372
9673L	Large	10.35	4.02	2.75	15.768 lb.	1.314
9673S	Small	9.48	3.50	2.5	13.512 lb.	1.126
9673XS	X - Small	9.15	3.35	2.5	12.588 lb.	1.049
9673M	Medium	10.00	3.74	2.75	14.364 lb.	1.197

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2021 MCR Safety - All Rights Reserved