




## Features

- 2700K color temperature
- High color rendering (90+ CRI)
- Low voltage - 12V DC operation
- Available in three puck kits or single pucks
- Recessed or surface mount design
- Low profile design - less than 3/4" high
- Dimmable with most TRIAC, CL, and ELV dimmers or Trulux single color control system
- Direct hardwire or plug-in installation
- cULus Listed for dry location
- 30,000 hours rated life

## Available Finishes



White    Nickel    Black

## Control Options

- Trulux Single Color Controls  
Requires Adaptive Driver + Trulux Receiver
- Primary Side Dimming  
Requires Standard Dimmer + Adaptive Driver

## Listing / Ratings




## Omni Puck - 12V

These low profile LED puck lights feature traditional hub system power input for recessed or surface mount applications. Available in three finishes, as single pucks or three puck kits, they can be controlled with the single color Trulux control system (no minimum load requirements) or using most TRIAC, CL or incandescent dimmers with ELV driver or PS-12-12VPI-T driver within minimum and maximum load requirements.

## Technical Information

Series	OMNI
Input Voltage	12V DC
CCT	2700K
CRI	90+
Wattage	3.2W per puck
Lumens	Up to 150Lm (see individual product)
Beam Angle	120°
Max Run	Dependent on driver, and dimming or non-dimming
Dimmable	15-100% (CL, ELV, TRIAC); 5-100% (Trulux)
Mounting	Surface or recessed (2-1/4" Dia. cut-out)
Rating	cULus Listed (dry location)
Rated Life	30,000 hrs



## Omni



Single Puck - White  
3.2W / 150Lm  
**OMNI-1-WH**



Single Puck - Nickel  
3.2W / 145Lm  
**OMNI-1-NK**



Single Puck - Black  
3.2W / 140Lm  
**OMNI-1-BK**

Omni Single Pucks Include: (1) Omni Puck with 72" lead wire / Mounting hardware

## Omni Kits



Three Puck Kit - White  
**OMNI-3KIT-WH**




Three Puck Kit - Nickel  
**OMNI-3KIT-NK**



Three Puck Kit - Black  
**OMNI-3KIT-BK**

Omni Three Puck Kits Include: (1) 12V DC plug-in driver with 3-port hub and rocker switch / (3) Omni Pucks with 72" lead wires / Mounting hardware

## Primary Side Dimming Set-up



CL/ELV Dimmer

+



Adaptive Series Power Supply  
(30W, 60W, 96W)

+



Omni Puck Lights

## Trulux Controller Set-up



Push Dial Controller  
(Single zone)

+



Adaptive Series Power Supply  
(30W, 60W, 96W)

+



Trulux RF Receiver  
(Required)

+



Omni Puck Light