



PIP® Whistler™

Vented, Cap Style Hard Hat with HDPE Shell, 4-Point Textile Suspension and Wheel Ratchet Adjustment

- Lightweight shell made with UV stabilized High Density Polyethylene (HDPE) reduces worker fatigue
- Shell design includes a rain trough for extra convenience in adverse weather conditions
- Vented to increase air flow and to reduce inside hard hat temperatures
- 4-Point quick release suspension with strong textile straps and crown comfort pad provides a comfortable and secure fit
- Non-chaffing, replaceable foam sweatband for maximum sweat absorption
- SURE LOCK wheel adjustment system for one hand size adjustments

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications

Technical Data

Color	Northern Blue, Sky Blue, White, Dark Green, Dark Gray, Royal, Hi-Vis Yellow, Lime, Pink, Navy, Black, Yellow, Gold, Orange, Light Blue, Hi-Vis Orange, Gray, Red
Sizes Available	OS
Packaging	Bagged Each
Packed	12/Case
Case Dimensions (in)	20.30 x 14.00 x 28.10
Case Weight (lbs)	14.55
Country of Origin	Canada
Shell Material	HDPE
Shell	Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Sweatband	Felt Lined Foam
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP241RV-11	Black	OS	620606006475	10616314798549	10620606006472
280-HP241RV-14	Dark Gray	OS	620606006505	620606006505	10620606006502
280-HP241RV-04	Dark Green	OS	620606006406	10620606006403	10620606006403
280-HP241RV-13	Gold	OS	620606006499	10616314398923	10620606006496
280-HP241RV-09	Gray	OS	620606006451	10620606006458	10620606006458
280-HP241RV-31	Hi-Vis Orange	OS	620606006550	10620606006557	10620606006557
280-HP241RV-44	Hi-Vis Yellow	OS	620606006567	10620606006564	10620606006564
280-HP241RV-06	Light Blue	OS	620606006420	10616314366243	620606006420
280-HP241RV-45	Lime	OS	620606006574	10620606006571	10620606006571
280-HP241RV-08	Navy	OS	620606006444	10620606006441	10620606006441
280-HP241RV-18	Northern Blue	OS	620606006536	10620606006533	10620606006533
280-HP241RV-03	Orange	OS	620606006390	10620606006397	10620606006397
280-HP241RV-20	Pink	OS	620606006543	10616314754668	10620606006540
280-HP241RV-15	Red	OS	620606006512	10620606006519	10620606006519
280-HP241RV-17	Royal	OS	620606006529	10620606006526	10620606006526
280-HP241RV-07	Sky Blue	OS	620606006437	10620606006434	10620606006434
280-HP241RV-01	White	OS	620606006376	10620606006373	10620606006373
280-HP241RV-02	Yellow	OS	620606006383	10620606006380	10620606006380