



Technical Data



Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.59 x 9.84 x 12.60
Case Weight (lbs)	14.33
Country of Origin	Malaysia
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Rubber
Temple	Rubber Tips
Base Curve	9.75
Certifications	ANSI Z87.1
Product Circularity	Recycled via Terracycle

Bouton® Optical Monteray II™

Rimless Safety Glasses with Black Temple, Clear Lens and Anti-Scratch Coating

- Lightweight design provides all day user comfort
- Soft pliable rubber temples eliminate any pressure points
- Soft nosepiece minimizes slippage and keeps glasses in place for a secure fit
- 9.75 Base curve lens
- Meets ANSI Z87.1+
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-04

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-MT-10070	Black	Clear	Clear	AS	899558001863	01616314121943	02616314121942
250-MT-10071	Black	Clear	Clear	AS/AF	899558001870	01616314156211	02616314156210
250-MT-10072	Black	Tinted	Gray	AS	899558001887	01616314121936	02616314121935
250-MT-10074	Black	Tinted	Amber	AS	899558001900	01616314133687	02616314133686
250-MT-10075	Black	I/O	Clear	AS	899558001917	01616314156228	02616314156227

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated