

Made of flexible materials for dexterity and fingertip sensitivity. PU fingertip-dipped.

TEGERA® 801

Learn more

ESD STANDARD GLOVE WITH GOOD FINGER GRIP

Our standard glove for ESD protection. Soft, smooth and highly breathable. 13 gg fibre to ensure all-day comfort. PU fingertip dipped for maximum grip. Made of flexible materials for dexterity and fingertip sensivity.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Comfortable
- Breathable

FUNCTIONS

- ESD
- Antistatic/ATEX
- Conforms with IEC 61340-5-1 (ESD)

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Abrasion injuries, Scratches, lacerations, Antistatic

PRIMARY ENVIRONMENTS OF USE
Dry environments, Clean environments

PRIMARY AREAS OF USE
Assembly, Electronics work, Inspection work, Installation work

PRIMARY INDUSTRIES OF USE
Automotive manufacturing, Electrical equipment manufacturing, Electronics manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing

TYPE OF WORK
Light weight

SPECIFICATION
TYPE ESD gloves, Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL Carbon, Polyester
LENGTH 195-250 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bulk pack
DIPPING Fingertip dipped
DIPPING MATERIAL PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Polyester, Carbon thread
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE
CE Cat. II
EAC TP TC 019:2011
EN ISO 21420:2020
EN 388:2016+A1:2018 0131X
IEC 61340-5-1:2016 R < 1.0 x 10^9 Ω
EN 16350:2014 R < 1,0 x 10^8 Ω
ANSI 3 ABR

SIZE		ARTICLE NUMBER	EAN
5	XXS	801-5	7340118397542
6	XS	801-6	7340118392981
7	S	801-7	7340118393070
8	M	801-8	7340118393162
9	L	801-9	7340118393254
10	XL	801-10	7340118393346
11	XXL	801-11	7340118393438
12	3XL	801-12	7340118393520

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.