




|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288196415 | <b>Size:</b>                  | 122x83x16 mm |
| <b>Part number:</b>    | 05078656001   | <b>Weight:</b>                | 81 g         |
| <b>Article number:</b> | 7775          | <b>Country of origin:</b>     | TW           |
|                        |               | <b>Customs tariff number:</b> | 82079099     |

- Square head insert tool 9x12 mm
- For torque wrenches from the Click-Torque X series with 9x12 mm mounting
- Application: Hexagon screw heads or nuts
- With safety pin
- The chrome-vanadium steel version makes the plug-in tools suitable for heavy loads

Open ring spanner insert, for hexagon screw heads or nuts; for torque wrenches of the Click-Torque X series with 9x12 mm holder.

**Web link**  
<https://www.wera.de/en/05078656001>

Wera - 7775  
05078656001 - 4013288196415

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Drive 9x12 mm

With pin lock

Chrome vanadium steel



For torque wrenches from the Click-Torque X series with 9x12 mm mounting.



Safe working and rapid tool change thanks to the pin lock of the insert tools.



The insert tools are suitable for high loads thanks to their chrome-vanadium steel design.

Further versions in this product family:

|                    |  |  |  |  |  |  |  |
|--------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|                    | mm                                                                                | mm                                                                                | mm                                                                                | mm                                                                                | mm                                                                                  | mm                                                                                  | mm                                                                                  |
| 05078650001        | 9x12                                                                              | 10                                                                                | 17.5                                                                              | 44.2                                                                              | 27.6                                                                                | 22.5                                                                                | 11.0                                                                                |
| 05078651001        | 9x12                                                                              | 11                                                                                | 17.5                                                                              | 44.5                                                                              | 27.9                                                                                | 22.6                                                                                | 11.0                                                                                |
| 05078652001        | 9x12                                                                              | 12                                                                                | 17.5                                                                              | 44.5                                                                              | 28.9                                                                                | 24.3                                                                                | 11.0                                                                                |
| 05078653001        | 9x12                                                                              | 13                                                                                | 17.5                                                                              | 46.0                                                                              | 29.1                                                                                | 25.5                                                                                | 11.0                                                                                |
| 05078654001        | 9x12                                                                              | 14                                                                                | 17.5                                                                              | 46.5                                                                              | 29.5                                                                                | 27.5                                                                                | 11.0                                                                                |
| 05078655001        | 9x12                                                                              | 17                                                                                | 17.5                                                                              | 48.5                                                                              | 31.9                                                                                | 32.5                                                                                | 11.0                                                                                |
| <b>05078656001</b> | <b>9x12</b>                                                                       | <b>18</b>                                                                         | <b>17.5</b>                                                                       | <b>49.3</b>                                                                       | <b>32.7</b>                                                                         | <b>33.5</b>                                                                         | <b>15.0</b>                                                                         |
| 05078657001        | 9x12                                                                              | 19                                                                                | 17.5                                                                              | 49.5                                                                              | 32.9                                                                                | 34.5                                                                                | 15.0                                                                                |
| 05078658001        | 9x12                                                                              | 22                                                                                | 17.5                                                                              | 51.7                                                                              | 35.1                                                                                | 39.6                                                                                | 15.0                                                                                |

## Web link

<https://www.wera.de/en/05078656001>

Wera - 7775

05078656001 - 4013288196415

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)