

## KT-LED4.5FB11-E12-9XX-C REPLACEMENT LAMP

### DESCRIPTION

4.5W B11 Lamp | 2700–3000K | ≥ 90 CRI | Straight-tip Chandelier



Enclosed  
Fixture Rated



**LAMP TYPE:** Filament B11

**BASE TYPE:** E12 (Candelabra)

**WATTAGE:** 4.5W

**COLOR TEMPERATURE:** 2700–3000K

**COLOR RENDERING INDEX (CRI):** ≥ 90

**WARRANTY:** 3 Years

**RATED LIFE:** L70 (15,000 Hours)



### TYPICAL APPLICATIONS

- Chandeliers
- Vanity Fixtures
- Decorative Accent Lighting
- Wall Sconces
- Pendant Lights

### PRODUCT FEATURES

- Energy efficient, 80%+ energy savings over legacy equivalents
- Lower heat generation than legacy equivalents
- Smooth, uniform dimming to 10%
- Filament-style LED construction offers unique traditional appearance for decorative and mood-sensitive applications
- HiCRI LEDs offer enhanced color rendering vs. 80 CRI LEDs, providing ideal clarity, representation, uniformity of illuminated area/objects
- Long life minimizes replacement and maintenance costs
- ANSI compliant construction ensures fitment for intended applications
- Suitable for use in wet locations
- Operating temperature range –4°F/–20°C to 95°F/35°C
- PF > 0.8
- Suitable for use in enclosed fixtures
- Complies with Part 15 of FCC
- Title 20 compliant

### PERFORMANCE SPECIFICATIONS


Keystone Catalog Number	Base Type	Rated Lamp Wattage	Legacy Equivalent Wattage	Color Temp	Lumens	Efficacy	Input Voltage	CRI	Beam Angle	Dimmable
KT-LED4.5FB11-E12-927-C	E12	4.5W	40W incandescent	2700K	360	80 lm/W	120V	≥ 90	360°	Yes
KT-LED4.5FB11-E12-930-C	E12	4.5W	40W incandescent	3000K	360	80 lm/W	120V	≥ 90	360°	Yes

\* Color Uniformity: CCT (Correlated Color Temperature) range as per guidelines outlined in ANSI C78.377-2017

## KT-LED4.5FB11-E12-9XX-C

### REPLACEMENT LAMP

#### PHYSICAL SPECIFICATIONS



#### LAMP DIMENSIONS

A (Diameter)	1.38"
B (Length)	3.86"

BASE TYPE: E12 (Candelabra)

#### PACKAGING

Carton Quantity	24 pcs
Carton Dimensions	13.00" × 5.10" × 4.72"
Carton Weight	2.65 lbs

#### ORDERING INFORMATION

ORDER CODE	EASY CODE	UPC
KT-LED4.5FB11-E12-927-C	EKP-68	843654123646
KT-LED4.5FB11-E12-930-C	TKJ-96	843654129488

#### CATALOG NUMBER BREAKDOWN

## KT-LED4.5FB11-E12-9XX-C

1 2 3 4 5 6 7 8 9

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Filament Bulb
- 5 Lamp Shape
- 6 Base Type
- 7 90 CRI
- 8 CCT
- 9 Clear Bulb