



<b>EAN:</b>	4013288120472	<b>Size:</b>	98x44x32 mm
<b>Part number:</b>	05003567001	<b>Weight:</b>	99 g
<b>Article number:</b>	8790 HMB	<b>Country of origin:</b>	TW
		<b>Customs tariff number:</b>	82042000

- 3/8" Zyklop socket
- For manual and power tool operations (non-impact)
- Knurling at lower end to enable easy gripping when used in manual applications
- Equipped with ball stop groove
- With Take it easy tool finder: colour coding by size


The Wera manual and machine socket (ISO 2725 part 3) can be used in manual and machine operations. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool. Slip-proof for easy grip even with oily hands. With ball stop groove. For external hexagon screws and bolts. Made of matte chrome-plated chrome-vanadium.

**Web link**  
<https://www.wera.de/en/05003567001>

Wera - 8790 HMB  
05003567001 - 4013288120472

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

### Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

### Manual and machine sockets



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

#### Web link

<https://www.wera.de/en/05003567001>

Wera - 8790 HMB

05003567001 - 4013288120472

Wera Werkzeuge GmbH







Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

## Further versions in this product family:

							
		mm	inch	mm	mm	mm	mm
05003551001	blau_307C	6.0	-	29.0	10.5	18.0	12.0
05003552001	gelb_123C	7.0	-	29.0	11.0	18.0	12.0
05003553001	leuchtpink_232 C	8.0	-	29.0	12.2	18.0	12.0
05003554001	gruen_363C	9.0	-	29.0	13.5	18.0	12.0
05003555001	leuchtgelb_yello wC	10.0	-	29.0	14.5	18.0	12.0
05003556001	cyan_2985C	11.0	-	29.0	16.0	18.0	12.0
05003557001	schwarz_blackC	12.0	-	29.0	17.0	18.0	12.0
05003558001	tuerkis_339C	13.0	-	29.0	18.5	20.0	12.0
05003559001	pink_241C	14.0	-	29.0	19.5	22.0	12.0
05003560001	weiss	15.0	-	29.0	21.0	24.0	12.0
05003561001	violett_2735C	16.0	-	30.0	22.0	24.0	12.0
05003562001	rot_200C	17.0	-	30.0	23.5	24.0	12.0
05003563001	leuchtgruen_37 5C	18.0	-	30.0	24.5	24.0	18.0
05003564001	blau_307C	19.0	-	30.0	26.0	24.0	18.0
05003565001	leuchtpink_232 C	20.0	-	30.0	28.0	25.0	18.0
05003566001	gruen_363C	21.0	-	30.0	28.0	25.0	18.0
<b>05003567001</b>	<b>leuchtgelb_yell owC</b>	<b>22.0</b>	<b>-</b>	<b>30.0</b>	<b>32.0</b>	<b>25.0</b>	<b>18.0</b>
05003568001	cyan_2985C	24.0	-	32.0	32.0	25.0	20.0
05003569001	leuchtgelb_yello wC	-	1/4"	29.0	11.0	18.0	12.0
05003570001	blau_307C	-	5/16"	29.0	12.2	18.0	12.0
05003571001	leuchtgruen_37 5C	-	11/32"	29.0	13.5	18.0	12.0
05003572001	rot_200C	-	3/8"	29.0	14.5	18.0	12.0
05003573001	violett_2735C	-	7/16"	29.0	16.0	18.0	12.0
05003574001	tuerkis_339C	-	1/2"	29.0	18.5	20.0	12.0
05003575001	pink_241C	-	9/16"	29.0	19.5	22.0	12.0
05003576001	schwarz_blackC	-	5/8"	30.0	22.0	24.0	12.0
05003577001	cyan_2985C	-	11/16"	30.0	23.0	24.0	18.0
05003578001	gelb_123C	-	3/4"	30.0	26.0	24.0	18.0
05003579001	blau_307C	-	13/16"	30.0	28.0	25.0	18.0
05003580001	leuchtgruen_37 5C	-	7/8"	30.0	32.0	25.0	18.0

## Web link

<https://www.wera.de/en/05003567001>

Wera - 8790 HMB

05003567001 - 4013288120472

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

**Web link**

<https://www.wera.de/en/05003567001>

Wera - 8790 HMB

05003567001 - 4013288120472

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)