

PORTABLE AIR INFLATOR

5A | 17 SLPM | 130 PSI

AL5



LITHIUM POWERED. PORTABLE AIR COMPRESSOR.

ULTRAFAST INFLATION.

Experience unparalleled speed with a high-efficiency motor that seamlessly inflates balls, bicycles, mountain bikes, motorcycles, and more within seconds. It can also fully inflate vehicle tires (0-40 PSI) within 6 minutes.

BATTERY-POWERED.

Powered by a lithium battery, it can fully inflate tires - cars, ATVs, lawnmowers, motorcycles, bicycles, balls, plus car top-offs - on a single charge. It's rechargeable within 48 minutes and can even charge mobile devices, like smartphones.

SMART PRESSURE.

An integrated pressure sensor and innovative pulse-width technology. It automatically shuts off while monitoring and measuring pressure without overinflating, providing precision accuracy.

NOCO

30339 Diamond Parkway, #102
Glenwillow, OH 44139 | USA
1.800.456.6626

no.co



ULTRA PORTABLE.

LITHIUM POWERED AIR COMPRESSOR


5A MOTOR



TOP OFF LOW TIRES IN UNDER 1 MIN.

*TIME TO INFLATE (*195 / 65R15 Tire)
35-40 PSI

INTUITIVE INTERFACE.



POWER BUTTON

AIR BUTTON

AIR PRESSURE
UP/DOWN
LED
FLASHLIGHT





30W USB-C Port

CHARGE WITH USB-C.

Rechargeable directly with its integrated USB-C port within 48 minutes. Plus, the power to charge your favorite devices, like phones, tablets, laptops, wearables, and more.

WHAT'S IN THE BOX



AL5 Portable Air Inflator

USB-C to
USB-C Cable 24"

Microfiber storage bag



User Guide



TECHNICAL SPECIFICATIONS

MAX AIRFLOW AT 0 PSI:	17 SLPM	
MAX PRESSURE:	130 psi / 8.96 bar / 896 kPa	
MOTOR RATING:	90W	
DUTY CYCLE:	20 min @ 50 PSI "ON" time/40 min "OFF" time	
MANUAL MODE DUTY CYCLE:	10 min "ON" time/50 min "OFF" time	
POWER TYPE:	USB-C	
OPERATING TEMPERATURE:	14° to 113° F (-10° to +45° C)	
STORAGE TEMPERATURE:	14° to 113° F (-10° to +45° C)	
CHARGING TEMPERATURE:	32° to 113° F (-10° to +45° C)	
WEIGHT:	1.8lb (0.82kg)	
WARRANTY:	1-Year Limited Warranty	
VOLUMETRICS:	Retail Packaging: Dimensions: 10.31" x 6.14" x 3.9" Weight: 2.99 lbs UPC: 0-46221-24026-9	Master Carton: Dimensions: 22.72" x 7.2" x 9.92" Weight: 14.29 lbs Quantity: 4 ITF-14: 10046221230038
	Inner Carton: Dimensions: 10.87" x 6.54" x 4.37" Weight: 3.25 lbs	Units Per Pallet: US: 160 units

NOCO

30339 Diamond Parkway, #102
Glenwillow, OH 44139 | USA
1.800.456.6626

no.co

