



PIP®

Seamless Knit Cotton / Polyester Glove with Double-sided EverGrip™ Nitrile Coating

- Seamless cotton/polyester knit shell is comfortable and flexible
- Double-sided Nitrile "MW" pattern provides superior grip and abrasion resistance compared to rubber or PVC coatings
- Coated with a special formulated nitrile to resist melting
- Acceptable for brief contact up to 450 degrees (Heat protection is subject to change based on how the glove is used in the application)
- Curved finger style provides an ergonomic, comfortable fit
- Knit Wrist helps prevent dirt and debris from entering the glove

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Parts and Materials
- Equipment Maintenance and Repair
- Parts Cleaning
- Fastening and Anchoring

Technical Data

Color	Natural
Sizes Available	S-L
Packaging	Bulk Pack
Packed	12 Dozen/Case
Case Dimensions (in)	20.00 x 12.99 x 16.00
Case Weight (lbs)	24.01
Country of Origin	United States
Liner Material	Cotton, Polyester
Coating	Nitrile
Coating Color	Rust
Grip	Pattern
Gauge	7
Cuff	Knit Wrist
Construction	Coated Seamless Knit
Certifications	21 CFR, TAA Compliant
Product Circularity	Reusable / Launderable Recycled via Terracycle

Care Instructions



Machine
Wash



Water Temp
40°C



Do Not
Bleach



Tumble Dry



Low Heat

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-27

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
38-720S	Natural	S	616314018336	01616314018336	02616314018336
38-720M	Natural	M	616314032677	01616314032677	02616314032677
38-720L	Natural	L	616314018343	01616314018343	02616314018343