

Top quality oil repellent full leather glove. Withstands contact heat up to 100°C/212°F.

TEGERA® 6615

Learn more

FOR GOOD GRIP IN OILY ENVIRONMENTS

Top quality oil repellent full leather glove. Water and oil repellent palm. Withstands contact heat up to 100°C/212°F. Perfect for good grip in harsh, slippery, oily, and greasy environments. High level of protection and good fingertip sensitivity. Made of full grain cowhide and polyester. By purchasing this product, you are supporting Leather Working Group certified tanneries.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Excellent grip in oily environments

FUNCTIONS

- Water and oil repellent

OGT™ LEATHER WORKING GROUP

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Prevents risk of: , Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Contact with oil

PRIMARY ENVIRONMENTS OF USE

Slippery environments, Oily and greasy environments

PRIMARY AREAS OF USE

Assembly, Engineering, Petro-chemical work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Metal manufacturing and fabrication, Transport equipment manufacturing, Oil and gas extraction, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves, Assembly gloves
CATEGORY Cat. II
PALM MATERIAL Full grain cowhide
BACK MATERIAL Full grain cowhide
LINING Unlined
LENGTH 220-275 mm
DEXTERITY 5
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 6/60
DISPLAY TYPE Thread
FASTENING Elasticated 180°
OUTER MATERIAL SPECIFICATION Leather

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018
3111X

EN 407:2020
413XXX

ANSI 3 ABR

Warning, in case of emergency, this model cannot be removed easily

FEATURES

Water repellent

SIZE		ARTICLE NUMBER	EAN
6	XS	6615-6	7340118334516
7	S	6615-7	7340118334547
8	M	6615-8	7340118334578
9	L	6615-9	7340118334608
10	XL	6615-10	7340118334639
11	XXL	6615-11	7340118334660
12	3XL	6615-12	7340118334691

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.