



EAN:	4013288234131	Size:	252x162x71 mm
Part number:	05006610001	Weight:	1131 g
Article number:	Kraftform Kompakt VDE 17 extra slim 2 Tool Finder	Country of origin:	CZ
		Customs tariff number:	82054000

- The 837 i RA bitholding screwdriver with a ratchet integrated in the handle ensures fast and safe working
- 817 VDE handle for Kraftform Kompakt interchangeable blades
- VDE blades (157 mm length) with practical spinning function, anti-roll protection and Take it easy tool finder: colour coding by profile and laser-engraved size indication
- 1x Knipex needle-nose combination pliers, 185 mm long
- Individually tested tools as per IEC 60900
- In a robust folding pouch
- Compatible with Wera 2go

21-piece tool set for working in a tensionless state and working at the approved voltage of 1,000 V. One 837 i VDE bitholding screwdriver with ratchet functionality, one 817 VDE bladeholding screwdriver; each for Wera VDE blades; 14 VDE blades (each 157 mm length) with reduced blade diameter (items Kraftform Kompakt 60 i Take it easy 0.4x2.5 and Kraftform Kompakt 67 i Take it easy TX 10 standard blade diameter), so that even low-lying screw and spring elements can be easily reached and operated. With Take it easy tool finder: colour coding by profile and laser-engraved size indication - for quick and easy identification of the required tool. Individually tested tools as per IEC 60900 at 10,000 V for safe working at the approved voltage of 1,000 V. 1x Knipex VDE 08 26 185 needle-nose combination pliers for easy cutting thanks to the high-reduction power joint; with cutting edges for soft, medium-hard and hard wire. Milled groove on the handle for secure holding and drawing of small workpieces such as nails, pins and bolts. Chrome-plated for better rust protection, with insulated multi-component handle sleeves. In a robust belt pouch. The textile box features a fleece zone at the back. Using the provided self-adhesive hook-and-loop fastener strips, the textile box can be attached to the Wera 2go components. Or to the wall, shelf or workshop trolley.



Web link

<https://www.wera.de/en/05006610001>

Wera - Kraftform Kompakt VDE 17 extra slim 2 Tool Finder
05006610001 - 4013288234131

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Individually tested



Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900. This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

The 837 i RA bladeholding screwdriver with ratchet functionality




The integrated ratchet with fine toothing (40 teeth and a return angle of 9°) eases and accelerates screwdriving without having to reposition the tool.

The handle/blade system – Kraftform Kompakt VDE



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

Easy change




The Kraftform Kompakt VDE blades can be replaced simply by pulling down the yellow ring on the handle.

PlusMinus screwdrivers




For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

VDE interchangeable blade with reduced shaft diameter (iS)




Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

Take it easy



The Kraftform Kompakt VDE blades are equipped with the Take it easy tool finder. Colour coding by profile and laser-engraved size indication make it easy to identify the required tool quickly.

Hexagonal anti-roll feature against rolling away



The Kraftform Kompakt blades come with an anti-roll protection. The hexagonal shape hinders the blade from rolling away annoyingly at the workplace.

Web link

<https://www.wera.de/en/05006610001>

Wera - Kraftform Kompakt VDE 17 extra slim 2 Tool Finder
05006610001 - 4013288234131

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

837 i RA Kraftform blade-holding handle with ratchet functionality, 9 x 115 mm



05057490001

1x 9 x 115 mm



817 VDE Kraftform blade-holding handle, 9 x 98 mm



05003990001

1x 9 x 98 mm



Kraftform Kompakt VDE 62 iS Take it easy, PH 1 x 157 mm



05006512001

1x PH 1 x 157 mm

05006513001

1x PH 2 x 157 mm



Kraftform Kompakt VDE 65 iS Take it easy, PZ 1 x 157 mm



05006526001

1x PZ 1 x 157 mm

05006527001

1x PZ 2 x 157 mm



Kraftform Kompakt VDE 65 iS PZ/S Take it easy, # 1 x 157 mm



05006530001

1x # 1 x 157 mm

05006531001

1x # 2 x 157 mm



Kraftform Kompakt VDE 67 i TORX® Take it easy, TX 10 x 157 mm

05006534001

1x TX 10 x 157 mm



Kraftform Kompakt VDE 67 iS TORX® Take it easy, TX 15 x 157 mm



05006540001

1x TX 15 x 157 mm

05006541001

1x TX 20 x 157 mm

05006542001

1x TX 25 x 157 mm



Kraftform Kompakt VDE 60 i Take it easy, 0.4 x 2.5 x 157 mm

05006500001

1x 0.4 x 2.5 x 157 mm



Kraftform Kompakt VDE 60 iS Take it easy, 0.6 x 3.5 x 157 mm



05006506001

1x 0.6 x 3.5 x 157 mm

05006507001

1x 0.8 x 4 x 157 mm

05006508001

1x 1 x 5.5 x 157 mm



KNIPEX Needle-nose combination pliers 08 26 185

1x KNIPEX Needle-nose combination pliers 08 26 185



Web link

<https://www.wera.de/en/05006610001>

Wera - Kraftform Kompakt VDE 17 extra slim 2 Tool Finder
05006610001 - 4013288234131

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Hook and Loop Fastener Strip 70, 50 x 70 mm

1x 50 x 70 mm



Web link

<https://www.wera.de/en/05006610001>

Wera - Kraftform Kompakt VDE 17 extra slim 2 Tool Finder
05006610001 - 4013288234131

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de