Path & Spread







Name	Stepped Dome	Traditional	Missionary Solid Brass
SKU # Finish	**15505CBR**	**15478AZT** **15478BKT** **15478CBR**	**15480CBR**
Socket Type	T3/G4 Bi-Pin	T3/G4 Bi-Pin	T3/G4 Bi-Pin
Dimensions	6.25"W x 6.25"L x 20.25"H	6.75"W x 6.75"L x 21"H	8.5"W x 8.5"L x 23.25"H
Included Accessories	Includes 8" slotted in-ground stake and locknut. 48" of usable #18-2, SPT-1W leads. Cable connectors included.	Includes 8" slotted in-ground stake, 2 gel-filled wire nuts, and locknut. 48" of usable #18-2, SPT-1W leads.	Includes 8" slotted in-ground stake and locknut. 30" of usable #18-2, SPT-1W leads. Cable connectors not included. Brass will naturally patina over time.
Optional Accessories	CBR 3" Mounting Base **15493**. 14" Stake **15576BK**. Power Post **15276BK**.	Surface Mounting Flange **15601AZT, BKT**. 3" Round Mounting Base **15493CBR**. 14" In-ground Support Stake **15576BK**. Power Post **15276BK**.	3" Round Mounting Base **15493CBR**. 14" In-ground Support Stake **15576BK**. Power Post **15276BK**.







Name	6" Dome	8" Dome	Short 8" Dome
SKU # Finish	**15470AZT** **15470BKT** **15470CBR**	**15310AZT** **15310CBR** **15310AZT6** **15310BKT**	**15410AZT**
Socket Type	T5 Wedge	T5 Wedge	T5 Wedge
Dimensions	6"W x L x 21"H	8.25"W x L x 21"H	8.25"W x L x 15"H
Included Accessories	Includes 8" slotted in-ground stake, 18" stem, locknut, and 16.25W(VA) 921X (17025) Xenon lamp. CBR version, lamp sold separately. 24" of usable #18-2, SPT-1W leads. Cable connectors included with AZT and BKT. Cable connectors not included with CBR.	Includes 8" slotted in-ground stake and locknut. 24" of usable #18-2, SPT-1W leads. Cable connectors included.	Includes 8" slotted in-ground stake, locknut, and 16.25W(VA) 921X (17025) Xenon lamp. 30" of usable #18-2, SPT-1W leads. Cable connectors included.
Optional Accessories	Surface Mounting Flange **15601**. Surface Mounting Bracket **15607**. 14" Stake **15576BK**. Power Post **15276BK**.	Surface Mounting Flange **15601**. Surface Mounting Bracket **15607**. 14" Stake **15576BK**. Power Post **15276BK**.	Surface Mounting Flange **15601**. Surface Mounting Bracket **15607**. 14" Stake **15576BK**. Power Post **15276BK**.