

MANUFACTURER Glyph Production Technologies
PRODUCT FAMILY BlackBox Plus

PRODUCT SKUS

Model	Capacity	RPM	Description	UPC
BBPL500	500 GB	7200	Glyph BlackBox Plus, 500GB, Bus-powered, 7200RPM, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450002371
BBPL1000B	1 TB	5400	Glyph BlackBox Plus, 1TB, Bus-powered, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450003262
BBPL1000	1 TB	7200	Glyph BlackBox Plus, 1TB, Bus-powered, 7200RPM, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450002388
BBPL2000	2 TB	5400	Glyph BlackBox Plus, 2TB Bus-powered, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450002395
BBPLSSD512	500 GB	SSD	Glyph BlackBox Plus, 512GB SSD, Bus-powered, SSD, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450002401
BBPLSSD1000	1 TB	SSD	Glyph BlackBox Plus, 1TB SSD, Bus-powered, SSD, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450002418
BBPLSSD2000	2 TB	SSD	Glyph BlackBox Plus, 2TB SSD, Bus-powered, SSD, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450003118
BBPLSSD3800	3.8 TB	SSD	Glyph BlackBox Plus, 3.8TB SSD, Bus-powered, SSD, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450003125
BBPLSSD7600	7.6 TB	SSD	Glyph BlackBox Plus, 7.6TB SSD, Bus-powered, SSD, USB-C (3.1) (Works with USB 3.0/2.0, Thunderbolt 3)	691450003132

PRODUCT TITLE Glyph Blackbox Plus Professional External Rugged Mobile Hard Drive

SHORT DESCRIPTION Rugged, potable, external desktop hard drive designed for creative professionals. Backed by the industry's best warranty.

LONG DESCRIPTION The Blackbox Plus by Glyph is a rugged, mobile hard drive designed for creative professionals. Featuring the latest USB-C technology, optimized cooling, and integrated health monitoring. Plus, it's built to take a beating. The Blackbox Plus is small enough to fit in your pocket, yet powerful enough to take it's rightful place in your workflow. All Glyph Professional products are assembled in the USA and backed by an industry leading warranty including data recovery and advance replacement.

FEATURES

- Works with USB-C, USB-3.0/2.0, Thunderbolt 3
- Up to 140 MB/s transfer rate (HDD)
- Up to 560 MB/s transfer rate (SSD)
- Bus-Powered
- Quiet Fanless Design
- Formatted for Mac, simple reformat for Windows use

DIMENSIONS

Box Dimensions	7.5" x 7" x 1.25"
Drive Dimensions	3.7" x 5.6" x .7"

RETAIL PACK WEIGHT 1.1 lbs

IN THE BOX

- BlackBox Plus External Hard Drive
- USB-C to USB-C cable
- USB-C to USB 3.0/2.0 Cable
- Rugged External Sleeve

WARRANTY 3 Years Hardware coverage, 2 Years Level-1 Data Recovery, 1 Year Advance Replacement

COMPATIBILITY Mac OS X 10.4 and above. Windows Vista and above. Formatted for Mac.

ACCESSORIES	Model	Description	UPC
	ASC1301	Glyph Carry Case Small	691450002289

RESELLER PORTAL <https://www.glyphtech.com/user>
(Login Required)

DATASHEET http://www.glyphtech.com/sites/default/files/product_documents/Datasheet%20-%20BlackBox-Plus.pdf

WEBSITE INFO <http://www.glyphtech.com/product/blackbox-plus>

COUNTRY OF ORIGIN Designed and assembled in the USA

