

8767 A HF TORX® Zyklop bit socket with holding function, 1/4" drive, TX 25 x 100 mm



EAN:	4013288186881	Size:	170x44x22 mm
Part number:	05003366001	Weight:	40 g
Article number:	8767 A HF	Country of origin:	CZ
		Customs tariff number:	82079030

- Bit socket (non-impact) for manual or machine tool operations
- The holding function holds screws securely on the tool
- With Take it easy tool finder: colour coding by size
- Knurling on lower end for more grip when used manually.
- Chrome vanadium steel, matte chrome-plated

Bit socket with 1/4" drive and holding function for particularly comfortable screwdriving with reduced risk of losing the screw when feeding it into the workpiece. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool .

Web link

<https://www.wera.de/en/05003366001>

Wera - 8767 A HF

05003366001 - 4013288186881

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Bit sockets with holding function for TORX® screws



The HF tools developed by Wera are ideal because they feature an optimised geometry of the original TORX® profile. The wedging forces resulting from the surface pressure between the drive tip and the screw profile mean that TORX® screws made according to Camcar Innovations, Michigan, USA specifications are securely held on the tool!

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).

Manual and machine sockets



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

Further versions in this product family:



mm



mm



mm



mm

			mm	mm	mm	mm
05003360001	iceblue_277C	TX 8	28.0	12.0	12.5	11.0
05003361001	tuerkis_339C	TX 9	28.0	12.0	12.5	11.0
05003362001	leuchtgruen_375C	TX 10	28.0	12.0	12.5	11.0
05003363001	leuchtgelb_yellowC	TX 15	28.0	12.0	12.5	11.0
05003364001	pink_241C	TX 20	28.0	12.0	12.5	11.0
05003365001	gelb_123C	TX 25	28.0	12.0	12.5	11.0
05003366001	gelb_123C	TX 25	100.0	12.0	12.5	83.0
05003367001	blau_307C	TX 27	28.0	12.0	12.5	11.0
05003368001	blau_307C	TX 27	100.0	12.0	12.5	83.0
05003369001	leuchtorange_152C	TX 30	28.0	12.0	12.5	11.0
05003370001	leuchtorange_152C	TX 30	100.0	12.0	12.5	83.0
05003371001	rot_200C	TX 40	28.0	12.0	12.5	11.0
05003372001	rot_200C	TX 40	100.0	12.0	12.5	83.0

Web link

<https://www.wera.de/en/05003366001>

Wera - 8767 A HF

05003366001 - 4013288186881

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de