

5m (15ft) Active High Speed HDMI Cable – HDMI to HDMI Micro – M/M

Product ID: HDADMM5MA



The HDADMM5MA Active HDMI to Micro HDMI cable features a built-in active signal booster that provides a connection distance of up to 15 feet (5m) between your HDMI Micro-equipped smartphone, tablet or other portable device and an HDMI-capable TV or display, with no signal loss.

This durable, lightweight cable features thinner HDMI wire construction - approximately half the thickness of a regular 5m cable, which allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the HDMI signal with no external power required.

The active booster circuit and thin wire construction design of this cable makes it perfect for any mobile user, from people on the move with hectic schedules to anyone wanting to connect from the comfort of their couch. The cable is portable enough that it fits nicely inside your laptop bag, ensuring you always have the right cable to connect your mobile device to an HDMI display, and is slim enough that it provides a convenient connection to your TV without the hassle of bulky cables getting in your way – and all without the need of an external power source.

This 5 meter Active HDMI cable is backed by StarTech.com's 2-year Warranty.

Please Note: This cable features unidirectional architecture which requires that it is installed in a specific direction. Please refer to the "Display" label on the HDMI connector which plugs into your display, in order to ensure that the device and the Micro HDMI source are connected properly.

Certifications, Reports and Compatibility

Applications

- Connect your HDMI Micro-equipped mobile device (Smartphone, Tablet, etc.) to an HDMI TV or display, up to 5m away, with no signal loss

Features

- Thin cable design (3.6mm OD) reducing bulkiness and adding flexibility
- Built-in, active amplifier circuitry
- Gold-plated HDMI connectors
- Supports Resolutions up to 4k x 2k

Hardware

Warranty	2 Years
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	Micro HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	36 AWG
Cable Length	16.4 ft [5 m]
Cable OD	0.1 in [3.6 mm]
Product Length	16.4 ft [5 m]
Product Width	7.6 in [19.3 cm]
Product Height	3.4 in [86 mm]

Weight of Product	3.6 oz [103 g]
-------------------	----------------

Packaging Information

Package Quantity	1
Package Length	15.6 in [39.5 cm]
Package Width	5.5 in [14 cm]
Package Height	0.7 in [17 mm]
Shipping (Package) Weight	3.7 oz [106 g]

What's in the Box

Included in Package	5m Active Slim High Speed HDMI to Micro HDMI Cable
---------------------	--

****Product appearance and specifications are subject to change without notice.***

