




QuickStand Series

Portable Frame-Folding Projection Screen

User's Guide






Setup Procedure

The frame and supports are made of 1 3/8" aluminum tubing with an anodized finish. Please follow the instructions in this package. With proper care, your QuickStand screen will provide many years of reliable service.

Two Section Frame

(For presentation screens that are less than 120" in diagonal measurement)

1. Take the frame out of the case and remove its wrappings. Unfold the main joints as shown in (fig 1).
2. Once the main joints are unfolded, make sure that the snap latches "click" into the locked position. The frame should now be fully elongated as in (fig2). **Note: The snap latches will automatically lock when the joint is straightened. Press the snap latch button in order to release the lock.*
3. While holding the bottom of the frame in place, lift the top of the frame to unfold the sides which will cause the snap latches lock when fully extended. Secure the corner braces into the locked position. The screen frame should now be fully opened as in (fig 3).



Three Section Frame

(For large presentation screens that are 120" or more in diagonal measurement)

1. Take the frame out of the case and remove its wrappings. Unfold the main joints making sure that both the end and middle spans are in perfect alignment as shown in (fig 4).
2. Make sure that the snap latches have locked the joints in the frame so that it is at its full horizontal extension as shown in (fig 5)
3. While holding the bottom of the frame in place, lift the top of the frame to unfold the sides which will cause the snap latches lock when fully extended. Secure the corner braces into the locked position. The screen frame should now be fully opened as in (fig 6).




fig 4



fig 5







fig 6



Standard T-Leg Support

1. Take the T-Leg out of the case and remove its wrappings. Fold down the support legs as shown in (fig 7).
2. Secure the corner braces into the locked position as shown in (fig 8)
3. Unfold the T-Leg's main support until the snap latches "click" into the locked position as in (fig 9).



AT-Leg (optional support buttress recommended for the large screens with diagonal measurements of 150" and over)

1. Take the AT-Leg buttress out of the case and remove its wrappings. Unfold the buttress as shown in (fig 10).
2. Snap latches will automatically lock in the center joint. Use the snap latch buttons to unlock the end joints as shown in (fig 11).
3. Attach the AT-leg to the T-Leg by securing the locking bolts through the frame using the frame spacers between the metal parts as shown in (fig 12) (*Note: It is important to always use the plastic frame spacers between the pieces whenever connecting any of the aluminum surfaces such as T-bars to AT, SAT and Frame components.)



SAT-Leg (optional added stability buttress recommended for the large screens with diagonal measurements of 180" and over)

1. Take the SAT-Leg out of the case and remove its wrappings as shown in (fig13).
2. Undo the snap locks to loosen and bend the joints for proper fitting as shown in (fig 14).
3. Attach the SAT-Legs by securing the locking bolts through the frame using the frame spacers between the metal parts as shown in (fig 15)




fig 13




fig 14






fig 15

Attaching the Frame to its Supports

1. Always use at least two locking bolts through the T-Leg Support, the Spacer and into the Frame on each side.
2. Height can be adjusted in 8" increments up or down. Normal screen height is 44" from the bottom of the frame to the floor.
3. Reverse this process to dismantle and pack away the screen.



Folding the Screen material for proper packing

Please observe the following precautions before folding up the screen material.

1. Do not bring the viewing surface into contact with chemical solvents, sharp or abrasive objects, painted, varnished or plastic finished items. (*See the cleaning instructions for exceptions to this)
2. Make certain that the screen is laid out on a dry, clean and flat surface.

Folding up the screen:

Lay out the screen with the viewing surface facing up and cover it with flat (not crumpled) tissue or packing paper that is clean and unprinted. *Note: Do not ever use abrasive paper, newspaper or any printed material on your projection screen.

1. With the viewing surface facing up, fold the fabric in half from top to bottom. When folding, make certain that the viewing surface does not come into contact with the black binding, grommets or snap buttons. *Note: The screens are shipped from production with tissue paper in the folds that should be retained for future use.

2. Make sure that the first folds never exceed 3 feet in width (fold again if necessary). Also make sure that there is always clean packing paper in between the two surfaces.
3. Larger sized screens will need to be folded with more frequency than smaller screens. Follow the instructions from step 1 as well.
4. Fold the material from top to bottom first then alternate in folding left to right until the material is of a sufficient size that will fit into the leatherette case.

Note: Keep the screen material inside its case when not in use. Failure to follow this precaution may eventually result in staining or discoloration.


Cleaning

The screen surface can be cleaned as follows.

Use a clean white cloth (100% cotton preferred) and dampen it with clear water. Gently wipe in one direction and NOT in a circular motion. Use another dry cloth to dry after each cleaning session. To remove a stubborn stain or sticky surface, use denatured alcohol (methanol or methyl alcohol) in lieu of water.

Attaching the Screen once it is unpacked

1. Using the snap buttons to connect the Screen material with the case
2. Start at the top working in whatever direction is most comfortable to you
3. Stretch the corners if necessary to pair up the buttons with their corresponding snaps



Parts List

1. Frame x 1 piece
2. Support (T) Legs x 2 pieces
3. AT-Legs x 2 pieces (optional depending on size)
4. SAT-Legs x 2 pieces. (optional depending on size)
5. Screen Fabric x 1 piece
6. Locking Bolt x 6-26 pieces
7. Frame Spacer x 6-26 pieces
8. User Guide x 1 pieces

Please make sure all parts listed are supplied. Should any parts be missing contact us at service@elitescreens.com

The following points should be noted to assure the sound performance and longevity of your screen

1. Never use your hand to touch the screen surface.
2. Never scrabble on the screen with anything.
3. Don't touch the screen with hard or sharp objects.
4. Please use a clean cotton cloth or soft dust brush to remove any dust particles on the screen.
5. The screen material may be cleaned

Limited Warranty Policy

What is Covered: Elite Screens, Inc. ("Elite Screens") warrants its products to the first retail purchaser, if purchased new and operated in the United States or Canada, to be free from defects in workmanship and materials (except as provided below) for a period of (2) years from the date of original purchase, and (3) years for products purchased directly by educational, non-profit, religious or government organizations.

Refurbished products purchased directly from Elite Screens are warranted for a period of (90) days from the date of original purchase.

For warranty service, you must provide proof of purchase and the serial number of your product.

How to Get Service: Should this product prove defective during the warranty period, please visit www.elitescreens.com/rmaform and submit a warranty claim form. You must provide your proof of purchase, the serial number of your product, and describe the problem you are experiencing with your screen. An Elite Screens representative will determine whether the product requires service, and provide you with further instructions on how to proceed with your warranty claim.

Missing Parts: If your product is missing parts, Elite Screens will, at its option, replace the part without any charge, including shipping and handling, provided that you report your claim within (7) days of receipt. If you report your claim after (7) days of receipt, but within (30) days of receipt, Elite Screens will, at its option, replace the part without charge, but you will bear the cost of shipping and handling. If you report your claim after (30) days of receipt, you will bear all costs to replace the part.

Returns and Exchanges: If a return is needed, Elite Screens will issue you a Return Merchandise Authorization ("RMA") Number. This number is valid for (45) days from the date of issue, and is required to process any returns. A returned item sent to Elite Screens without a visible or valid RMA Number is subject to refusal by Elite Screens. You are responsible for the cost of returning the item and ensuring the product is properly packaged to prevent damage in transit.

Once a returned product is received, Elite Screens will, at its option, replace the product or part without charge, including ground service freight. The replacement product or part may be new or refurbished to the Elite Screens standard of quality, and is subject to stock availability. Elite Screens' liability for replacement of the covered product will not exceed the original retail selling price of the covered product. Exchange products and parts assume the remaining warranty period of the original product covered by this limited warranty.

What is Not Covered: This warranty is not transferable and does not cover product purchased by another end user. This warranty does not cover incidental damages, such as loss of time, loss of use, or installation costs of defective, repaired or replaced product. This warranty does not cover product that has been damaged or rendered defective as a result of (a) neglect, abuse or misuse; (b) modification of the original product; (c) improper use or installation of products not manufactured by Elite Screens; (d) service provided by anybody other than Elite Screens; (e) abnormal mechanical or environmental conditions; (f) unusual physical or electrical stress -including failure or fluctuation of electrical power, lighting, static electricity, fire, tornadoes, or other natural disasters.

Elite Screens does not warrant against freight damage, concealed or otherwise, unless product is shipped directly from an Elite Screens facility. You must contact the vendor and the delivering carrier to report freight damage within (7) days of receipt. Failure to report freight damages within the carrier's guidelines may result in you bearing all costs.

THIS LIMITED WARRANTY AND REMEDY PROVIDED ABOVE ARE EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES. ELITE SCREENS, INC. DISCLAIMS ALL OTHER WARRANTIES, WHETHER EXPRESS, IMPLIED OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY, ANY WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE AND ANY IMPLIED WARRANTIES ARISING FROM A COURSE OF DEALING OR USAGE OF TRADE. THIS LIMITED WARRANTY GIVES THE END USER SPECIFIC LEGAL RIGHTS, AND THE END USER MAY HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.

EXCEPT AS PROVIDED IN THIS WRITTEN WARRANTY, ELITE SCREENS, INC. SHALL NOT BE LIABLE FOR ANY LOSS, INCONVENIENCE, OR DAMAGE, INCLUDING DIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES, RESULTING FROM THE USE OR INABILITY TO USE THE ELITE SCREENS PRODUCT, OR FOR LOST DATA OR LOST SOFTWARE WHETHER RESULTING FROM BREACH OF WARRANTY OR ANY OTHER LEGAL THEORY. SOME STATES DO NOT ALLOW THE EXCLUSION OR LIMITATION OF INCIDENTAL AND CONSEQUENTIAL DAMAGES, SO THE ABOVE LIMITATION MAY NOT APPLY.

In Canada, warranties include both warranties and conditions. Some jurisdictions do not allow limitations on how long an implied warranty lasts and some jurisdictions do not allow the exclusion or limitation of incidental or consequential damages, so the above limitations and exclusions may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from jurisdiction to jurisdiction.

International Warranty: Elite Screens, Inc. does not provide warranty coverage outside of the United States or Canada. For more information on the warranty coverage, terms and conditions in your region, contact your Elite Screens International Distributor directly.