

MaxLite® SL3 Series Linear LED Shop Light



General Safety Information

Please read and understand this entire manual before attempting to assemble, operate or install the product.



WARNING: RISK OF SHOCK

- House electrical current can cause painful shock or serious injury unless handled properly. For your safety, always remember to:
 - Turn off the power at the fuse or circuit breaker box before you install the shop light.
- This shop light is designed for use in a circuit protected by a fuse or circuit breaker. This shop light is intended to be installed directly beneath a ceiling-mounted receptacle and any excess cord should be kept out of the workspace. It is also designed to be installed in accordance with local electrical codes. If you are unsure about your wiring, consult a qualified electrician or local electrical inspector, and consult your electrical code.
- Account for small parts and destroy packing material, as these may be hazardous to children.

WARNING: RISK OF INJURY

- Do not open shop light. No serviceable parts inside.

WARNING: RISK OF FIRE

- Most dwellings built before 1985 have a supply wire rated 60°C. Do not overload the circuit and wiring. Consult a qualified Electrician.
- This device complies with part 15 of the FCC Rules. Operation is subject to the following 2 conditions:
 - (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures: Reorient or relocate the receiving antenna. Increase the separation between the equipment and receiver. Connect the equipment into an outlet on a circuit different from that to which the receiver is connected. Consult the dealer or an experienced radio/TV technician for help.
- Not for use with dimmers.
- This portable luminaire has a polarized plug (one blade is wider than the other) as a feature to reduce the risk of electric shock. This plug will fit in a polarized outlet only one way. If the plug does not fit fully in the outlet, reverse the plug. If it still does not fit, contact a qualified electrician. Never use with an extension cord unless plug can be fully inserted. Do not alter the plug.


MODELS

SL3-4823-50

SL3-4823-502PK

INCLUDED IN BOX

- A – (1) Fixture Assembly
- B – (2) “S” Hooks
- C – (2) Chain Hangers
- D – (2) Screw Type Eye Hooks
- E – (4) Wall Anchors
- F – (1) Cable Tie
- G – (2) ST4*30 Screws



MaxLite® SL3 Series Linear LED Shop Light



Installation Instructions

PREPARATION

Before beginning installation of the product, make sure all parts are present. If any part is missing or damaged, do not attempt to assembly, install or operate the product.

Estimated Assembly Time: 10 Minutes

Rated: 120V 60Hz 23W 0.215A

HANGING INSTALLATION

1. Install "screw eye hooks" (D) into ceiling (see warning below). (Recommend the plastic wall anchors (E) be used if mounting onto plaster board). See Figure 1.

WARNING: "Screw eye hooks" are for mounting onto wood ceiling or a plaster board surface (Recommend minimum 3/8" thick). Install each screw eye hook (D) or other mounting/hook option exactly 45.86 inches apart. Check to make sure the hold is secure and appropriate for the weight of the shop light. Never hang on the shop light or hang any object from the shop light.

WARNING: DO NOT INSTALL on radiant-heating ceilings.

WARNING: These hooks are to engage the hanging chain only and not the electric cord.

2. Slide the "S" hook (B) through the hang hole at the top of the end cap of the shop light assembly (A) and the end of the chain (C), and press the two ends of the hook tightly with pliers.
3. Attach the chains (C) to the "screw eye hook" (D) or other hook type that fits your ceiling. After the shop light is hanging, check whether it is securely installed. See Figure 2.
4. Plug the power cord into an outlet rated 120 V / 60 Hz. See Figure 3.

OPTIONAL FLUSH MOUNT INSTALLATION

1. Install 2 screws (G) on the mounting surface spaced 45.86 inches apart. Leave approximately 0.12" between the surface and screw. (Recommend the plastic wall anchors be used if mounting onto plaster board). See Figure 4.
2. Align the shop light to the screws and slide to one side to secure it in place. The shop light should be firmly fixed against the screws. If not firmly fixed, remove the shop light and tighten the screws to a smaller gap distance to the surface. See Figure 5.
3. Plug the power cord into an outlet rated 120 V / 60 Hz. See Figure 3

LINKING MULTIPLE SHOP LIGHTS

1. Insert the lamp plug of the required link into the socket of the previous lamp.

WARNING: The maximum number of connected lamps is 4.

WARNING: Do not link other electrical appliances.

FIGURE 1




FIGURE 2




FIGURE 3




FIGURE 4





FIGURE 5



MaxLite® SL3 Series Linear LED Shop Light



Warranty Information

MaxLite Inc. warrants its products for a minimum period of **FIVE (5)** years from the date of original purchase from MaxLite or its authorized distributor/dealer (the "Warranty Period"), as follows: If a Product fails to operate during the Warranty Period as a result of defects in materials or workmanship, MaxLite will, at its option, repair it, replace it with the same or like Product.

Please refer to Maxlite's website ([at http://maxlite.com/resources/warranties](http://maxlite.com/resources/warranties)) for the complete terms and conditions of our warranty.

Limitation of Liability

THE FOREGOING WARRANTY IS EXCLUSIVE, AND IS THE SOLE REMEDY FOR ANY AND ALL CLAIMS, WHETHER IN CONTRACT, IN TORT OR OTHERWISE ARISING FROM THE FAILURE OF PRODUCT AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ALL WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, WHICH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED TO THE EXTENT PERMITTED BY LAW AND, IN ANY EVENT, SHALL BE LIMITED TO THE WARRANTY PERIOD SPECIFIED ABOVE. THE LIABILITY OF MAXLITE SHALL BE LIMITED TO THE TERMS OF THE EXPRESS WARRANTY SET FORTH HEREIN. IN NO EVENT WILL MAXLITE BE LIABLE FOR ANY SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES INCLUDING, WITHOUT LIMITATION, DAMAGES RESULTING FROM LOSS OF USE, PROFITS, BUSINESS OR GOODWILL, LABOR COSTS, REMOVAL OR INSTALLATION COSTS, DECREASE IN THE LIGHT OUTPUT OF THE LAMP, AND/OR DETERIORATION IN THE LAMP'S PERFORMANCE, WHETHER OR NOT MAXLITE HAS BEEN ADVISED OF THE POSSIBILITY THEREOF. UNDER NO CIRCUMSTANCES SHALL MAXLITE'S ENTIRE LIABILITY FOR A DEFECTIVE PRODUCT EXCEED THE PURCHASE PRICE OF THAT PRODUCT. WARRANTY SERVICES PROVIDED UNDER THESE TERMS AND CONDITIONS DO NOT ENSURE THE UNINTERRUPTED OPERATION OF PRODUCTS; MAXLITE SHALL NOT BE LIABLE FOR DAMAGES CAUSED BY ANY DELAYS INVOLVING WARRANTY SERVICE.

This Limited Warranty gives you specific legal rights and you may also have other rights that may vary from state to state. Because some states or jurisdictions do not allow the exclusion or limitation of liability for consequential or incidental damages, this limitation may not apply to you.