

## Evanescence B Series Dimensions Table

Below Ceiling Installation																			
Unit: Inches																			
Model Number	Diag. Size	Aspect Ratio	Overall Length (A)	View Width (A1)	L/R Black Masking (A2)	Screen Width	Weight Bar Length (A3)	Case Length (A4)	A5	Overall Height (B)	View Height (B1)	Top Black Masking Border (B2)	B3	Case Height (B4)	Screen Height (B5)	C	C1	C2	C3
EB92HW2-E12	92"	16:9	90.2	80.2	2.0	84.2	87.6	87.8	89.0	63.9	45.1	12.0	3.0	3.7	60.1	4.3	3.1	4.7	89.8
EB100VW2-E12	100"	4:3	90.2	80.0	2.0	83.9	87.6	87.8	89.0	78.7	60.0	12.0	3.0	3.7	75.0	4.3	3.1	4.7	89.8
EB120VW2-E8	120"	4:3	106.1	96.0	2.0	99.9	103.5	103.7	104.9	86.7	72.0	8.0	3.0	3.7	83.0	4.3	3.1	4.7	105.7
EB100HW2-E12	100"	16:9	97.3	87.2	2.0	91.1	94.8	95.0	96.1	67.8	49.0	12.0	3.0	3.7	64.0	4.3	3.1	4.7	96.9
EB110HW2-E12	110"	16:9	106.1	95.9	2.0	99.8	103.5	103.8	105.0	72.7	54.0	12.0	3.0	3.7	69.0	4.3	3.1	4.7	105.7
EB120HW2-E8	120"	16:9	114.7	104.6	2.0	108.5	112.2	112.4	113.5	73.5	58.8	8.0	3.0	3.7	69.8	4.3	3.1	4.7	114.3
EB100HW2-E8	100"	16:9	97.3	87.2	2.0	91.1	94.7	94.9	96.1	63.7	49.0	8.0	3.0	3.7	60.0	4.3	3.1	4.7	96.9

  

Unit: mm																			
Model Number	Diag. Size	Aspect Ratio	Overall Length (A)	View Width (A1)	L/R Black Masking (A2)	Screen Width	Weight Bar Length (A3)	Case Length (A4)	A5	Overall Height (B)	View Height (B1)	Top Black Masking Border (B2)	B3	Case Height (B4)	Screen Height (B5)	C	C1	C2	C3
EB92HW2-E12	92"	16:9	2291	2037	50	2139	2225	2230	2261	1623	1146	305	76	94	1527	110	80	120	2281
EB100VW2-E12	100"	4:3	2290	2032	50	2132	2225	2230	2260	2000	1524	305	76	95	1905	110	80	120	2280
EB120VW2-E8	120"	4:3	2695	2438	50	2538	2630	2635	2665	2203	1829	203	76	95	2108	110	80	120	2685
EB100HW2-E12	100"	16:9	2472	2214	50	2314	2407	2412	2442	1721	1245	305	76	95	1626	110	80	120	2462
EB110HW2-E12	110"	16:9	2695	2435	50	2535	2630	2636	2666	1847	1371	305	76	95	1752	110	80	120	2685
EB120HW2-E8	120"	16:9	2914	2657	50	2757	2849	2854	2884	1868	1494	203	76	95	1773	110	80	120	2904
EB100HW2-E8	100"	16:9	2471	2214	50	2314	2406	2411	2441	1619	1245	203	76	95	1524	110	80	120	2461

Note: Data Error may be ±1"

The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.

