

USB to DVI Adapter – 1920x1200

Product ID: USB2DVIE3



The USB2DVIE3 USB DVI Video Adapter offers a perfect external multi-monitor solution, enabling you to add a high-resolution (up to 1920x1200) external DVI output to your desktop or laptop computer system using an available USB 2.0 port.

A cost-effective solution for systems that lack the outputs required for a multi-monitor setup, this high-performance USB to DVI adapter can be used to mirror your primary display and show the same image on both screens, or extend your desktop to double your workspace.

This small form factor USB video adapter can be used with up to 4 additional (5 total) USB2DVIE3 USB video adapters, creating multiple DVI connections to add additional displays quickly and easily - all without having to open the computer case to add extra video cards.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to five) monitors/projectors to your computer setup using one USB2DVIE3 device for each additional display
- View large or multiple spreadsheets that span multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display

- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

Features

- Supports resolutions up to 1920x1200
- Includes DVI to VGA Adapter and supports the use of DVI to HDMI adapters
- Works with desktop and laptop computers
- No power adapter required, easy installation

Hardware

Warranty	2 Years
AV Input	USB 2.0
AV Output	DVI
USB Pass-Through	No
Memory	32MB
Industry Standards	USB 2.0 Compliant
Chipset ID	Trigger - T2-285B

Performance

Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720 Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
Wide Screen Supported	Yes



General Specifications	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.
------------------------	--

MTBF	200,000 Hours
------	---------------

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
-------------	----------------------------

Connector B	DVI-I (29 pin)
-------------	----------------

Software

OS Compatibility	Windows 10 (32/64)
	Windows 8 / 8.1 (32/64)
	Windows 7(32/64)
	Windows Vista (32/64)
	Windows XP (32/64)

Special Notes / Requirements

System and Cable Requirements	System Processor: Quad Core 2.4GHz (i5 recommended)
	System Memory: 4GB

Note	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as DisplayLink or Fresco Logic
------	--

Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system resources

This USB video adapter is not intended for graphical intensive applications, such as gaming

Environmental


Operating Temperature	-10C to 55C (14F to 131F)
-----------------------	---------------------------

Storage Temperature	-25C to 75C (-14F to 167F)
---------------------	----------------------------

Humidity	<85% RH non condensing
----------	------------------------

Physical Characteristics

Color	Black
-------	-------



Material	Plastic
Cable Length	19.7 in [50 cm]
Product Length	3.5 in [88.0 mm]
Product Width	2.1 in [52.5 mm]
Product Height	0.7 in [18.0 mm]
Weight of Product	3.8 oz [108.0 g]

Packaging Information

Package Length	8.4 in [21.3 cm]
Package Width	5.7 in [14.6 cm]
Package Height	1.6 in [40.0 mm]
Shipping (Package) Weight	10.7 oz [304.0 g]

What's in the Box

Included in Package	USB to DVI adapter
	DVI to VGA adapter
	driver and software CD
	instruction manual

****Product appearance and specifications are subject to change without notice.***

