

Stock Code: **62300LEDDL-ML**

Collection: Iconic

PRODUCT INFORMATION

Base: 62300 Parent: 62300LEDDL
Mounting Type: Wall UPC: 641594235418
Finish: Matte Black
Diffuser: N/A

PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length
Width: 5"	Width:
Diameter	Diameter: 5"
Height: 12"	Height:
Extension: 4.5"	
Overall Height: 21"	

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

Frame Material: Metal
Diffuser Material: N/A
Lamping Type: E-26 (Replaceable LED Jbox: Standard
Lamping Base: E-26 Lamp Wattage: 7 W
Lamp Quantity: 2 Total Wattage: 14 W
Voltage: 120v Lamps Included: Yes

QUALIFICATIONS

Location Rating: Damp
Certification: UL (US/Canada) Listed
ADA Compliant: No Energy Star: No
JA8 Compliant: Yes Emergency Lighting: No
Marine Grade: No Warranty: 1 Year

PHOTOMETRICS

Dimmable: Yes Nominal Lumens: 1200 Lm
CRI: 90 Delivered Lumens: N/A
CCT: 2700K

Recommended Dimmers:

(TRIAC)LUTRON Ariadni/Toggler TGCL-153P; (TRIAC)LEVITON illumatech IPI06; (TRIAC)LUTRON Skylark CL SCL-153 or SCL-153P; (TRIAC)LEVITON Trimatron 6684; (TRIAC)LUTRON Diva DVCL-153P; (ELV)LUTRON Diva DVELV-303P; (TRIAC)LUTRON Skylark S-600 or S-600P

Additional Notes:

Multi-Directional Mounting; Custom Finish 5 Piece Minimum Order Quantity

Project Name: _____

Location: _____


Type: _____

Quantity: _____

Notes: _____



LINE DRAWING



IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: _____

Print Name _____ Date: _____

Toll Free 800-828-5483 www.AccessLighting.com

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice.

11/8/2022

62300LEDDL-ML.pdf

