

Stock Code: **63143LEDD-BS/SDG**

Collection: Port Nine Martini

### PRODUCT INFORMATION

Base: 63143 Parent: 63143LEDD  
Mounting Type: Wall UPC: 641594240061  
Finish: Brushed Steel  
Diffuser: Seeded Glass

### PRODUCT MEASUREMENTS

| FIXTURE          | BACKPLATE / CANOPY |
|------------------|--------------------|
| Length:          | Length             |
| Width: 8"        | Width: 4.5"        |
| Diameter         | Diameter:          |
| Height: 11.5"    | Height: 4.5"       |
| Extension: 9.75" |                    |
| Overall Height:  |                    |

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Steel  
Diffuser Material: Glass  
Lamping Type: SSL (Dedicated LED) Jbox: Standard  
Lamping Base: SSL Lamp Wattage: 9 W  
Lamp Quantity: 1 Total Wattage: 9 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating Damp  
Certification: ETL (US/Canada) Listed  
ADA Compliant: No Energy Star: No  
JA8 Compliant: Yes Emergency Lighting: No  
Marine Grade: No Warranty: 5 Year

#### PHOTOMETRICS

Dimmable: Yes Nominal Lumens 600 Lm  
CRI: 90 Delivered Lumens: 506 Lm  
CCT: 3000K  
Recommended Dimmers:  
(ELV)LUTRON Caseta PD - 6WCL; (TRIAC)LEVITON Decora Sureslide 6672; (TRIAC)LEVITON Decora Sureslide 6674;  
(ELV)LUTRON Maestro CL (Package) MACL-153M-RHW;  
(ELV)LUTRON Skylark Contour CTCL-153P; (TRIAC)LUTRON Ariadni/Toggler TGCL-153P; (TRIAC)LUTRON Diva DV


#### Additional Notes:

Can be Mounted Bulb Up or Bulb Down; Custom Finish 100 Piece Minimum Order Quantity; Optional Color Temperature 100 Piece Minimum Order Quantity


Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Quantity: \_\_\_\_\_  
Notes: \_\_\_\_\_



#### LINE DRAWING



#### IES FILE



In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice.

11/8/2022

63143LEDD-BS\_SDG.pdf

