



STAINLESS STEEL

PASS-THRU SHELF with Overshelf



Item #: _____ Qty #: _____
 Model #: _____
 Project #: _____



FEATURES:

Includes 1 Pass-Thru Shelf with 1 Overshelf
 Ships Assembled

Pass-Thru Features:

New Hat Channel design allows lower shelf to be freely positioned
 Includes Wall Mounting Brackets for securing lower Shelf to desired position
 Furnished with 1-1/2" sanitary roll down along length.
 Ends are square with 1-1/2" turn down at wall dimension.

Overshelf Features:

1-5/8" Stainless Steel Tubing Posts

CONSTRUCTION:

All TIG welded. Exposed welded areas polished to match adjacent surface.

MATERIAL:

18 gauge type "430" stainless steel and Brackets.
 Heavy Gauge Galvanized Hat Channel.



"L" BRACKET

18" Wide Shelves include "L" Brackets



CANTILEVER BRACKET

24" Wide Shelves include Cantilever Brackets

Length	18" WIDE	Wt.	24" WIDE	Wt.
48"	PA-18-48-2	100 lbs.	PA-24-48-2	116 lbs.
60"	PA-18-60-2	122 lbs.	PA-24-60-2	138 lbs.
72"	PA-18-72-2	152 lbs.	PA-24-72-2	170 lbs.
84"	PA-18-84-2	176 lbs.	PA-24-84-2	200 lbs.
96"	PA-18-96-2	232 lbs.	PA-24-96-2	256 lbs.
108"	PA-18-108-2	252 lbs.	PA-24-108-2	280 lbs.
120"	PA-18-120-2	280 lbs.	PA-24-120-2	306 lbs.
132"	PA-18-132-2	300 lbs.	PA-24-132-2	336 lbs.
144"	PA-18-144-2	330 lbs.	PA-24-144-2	364 lbs.



Customer Service Available To Assist You **1-800-645-3166** 8:30 am - 7:00 pm E.S.T.

For Orders & Customer Service:

Email: customer@advancetabco.com or Fax: 631-242-6900



For Smart Fabrication™ Quotes:

Email: smartfab@advancetabco.com or Fax: 631-586-2933


DETAILS and SPECIFICATIONS

TOL ± .500"


ALL DIMENSIONS ARE TYPICAL



Top View of Shelf




Bottom View of Shelf



3" x 4" L shape Mounting Bracket
Supplied with 18" Shelf

"L" Bracket Detail

Bottom View of Shelf



5" x 7" Cantilever Mounting Bracket
Supplied with 24" Shelf

Cantilever Bracket Detail

