



Technical Data

Color	Yellow
Sizes Available	10-18
Packaging	Bulk Pack
Packed	144/Case
Case Dimensions (in)	17.99 x 12.00 x 9.00
Case Weight (lbs)	9.99
Country of Origin	United States
Liner Material	Kevlar
Top of Arm	Elastic Cuff
Finger & Thumb	Thumb Hole
Ply	2-Ply
Lining	--
Construction	Seamless Knit
Certifications	TAA Compliant
Product Circularity	Reusable / Launderable Recycled via Terracycle

Kut Gard®

2-Ply DuPont™ Kevlar® Sleeve with Thumb Hole

- Kevlar provides excellent cut protection and heat resistance for the wrists and arms
- Seamless knit for comfort and flexibility
- 2-Ply construction for added protection
- Integrated thumb hole allows protection all the way to the knuckle without sacrificing dexterity

Applications

- Cut Resistance with Light Heat Protection
- Automotive Applications
- Glass Operations
- Light Heat Applications

Performance Data

ANSI Cut Level (2016)	A3
ANSI Puncture Level	--
ANSI Contact Heat Level	--
ASTM F1358 Vertical Flame Level	--

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-22



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
10-KS22TO	Yellow	22	616314026898	01616314026898	02616314026898
10-KS24TO	Yellow	24	616314026911	01616314026911	02616314026911
10-KS10TO	Yellow	10	616314026751	01616314026751	02616314026751
10-KS12TO	Yellow	12	616314026782	01616314026782	02616314026782
10-KS14TO	Yellow	14	616314020209	01616314020209	02616314020209
10-KS18TO	Yellow	18	616314017056	01616314017056	02616314017056