

These neoprene work gloves offer a rough finish dip that makes handling wet, slippery materials easier and safer.

- These neoprene work gloves are 100% liquid proof.
- Soft stretchy knit liner .
- Excellent wet grip. Safer handling means increased productivity.
- Extremely comfortable to wear.



Industries

- Automotive
- Chemical
- Automotive Aftermarket
- Logistics
- Machinery and Equipment
- Oil and gas
- Warehousing

Applications

- Equipment repair & maintenance
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Cleaning furnaces, distillation pumps, valves or lines and crackers BTX process


Previously known as: Scorpio™ 08-352

Key Features

- Cushions the hand, absorbs perspiration and prevents chafing
- Excellent wet grip. Safer handling means increased productivity
- Exceptional flexibility. Easier to manipulate, less tiring to the hand, incorporating easy donning and removal
- Neoprene coating for a wide range of chemical protection
- Textured finish for better grip on wet and slippery materials



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 08-352	Interlock cotton, Neoprene,	7, 8, 9, 10	305 mm / 12 inches	Green	• 12 pairs in a box, 6 boxes in a carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.