



G-Tek® 3GX®

Seamless Knit Dyneema® Diamond Blended Glove with Polyurethane Coated Flat Grip on Palm & Fingers

- Seamless construction offers increased comfort and breathability
- Dyneema® Diamond & Spandex shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Polyurethane coatings take on the surface properties of the glove liner providing a tactile grip in dry and slightly oily conditions, ideal for applications that require dexterity for precise handling
- Knit Wrist helps prevent dirt and debris from entering the glove
- Color coded hems for easy size identification
- Washable, resistant to chemicals, water, and ultraviolet light
- ⚠️ **WARNING:** Cancer - www.P65Warnings.ca.gov

Applications

- Thin Coating, Good Grip for High Dexterity Handling
- Maintenance and Repair Operations
- Handling, Assembly and Sorting of Small to Medium Parts and Materials
- Shipping, Receiving and Packaging



Technical Data

Color	Gray
Sizes Available	XS-2XL
Packaging	Pair Bagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	11.81 x 12.60 x 14.17
Case Weight (lbs)	11.68
Country of Origin	China
Liner Material	Dyneema Diamond Technology
Coating	Polyurethane
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Flat
Gauge	13
Cuff	Knit Wrist
Impact Protection	--
Construction	Coated Seamless Knit
Certifications	--
Product Circularity	Reusable / Launderable Recycled via TerraCycle

Performance Data

ANSI Cut Level (2016)	A3
ANSI Abrasion Level	3
ANSI Puncture Level	--
ANSI Impact Level	--
ANSI Contact Heat Level	--
EN 388	4442CX
ASTM F1358 Vertical Flame Level	--
EN 407	--

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-19



SPECIFICATION SHEET

STYLE: 19-D326

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
19-D326/XS	Gray	XS	616314167690	01616314167699	02616314167698
19-D326/S	Gray	S	616314167676	01616314167675	02616314167674
19-D326/M	Gray	M	616314167669	01616314167668	02616314167667
19-D326/L	Gray	L	616314167652	01616314167651	02616314167650
19-D326/XL	Gray	XL	616314167683	01616314167682	02616314167681
19-D326/XXL	Gray	2XL	616314167706	01616314167705	02616314167704

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-19