




The Scout™

OTG Rimless Safety Glasses with Clear Temple and Clear Lens

- Polycarbonate unilens
- Over-the-glass design fits over all prescription eyewear
- Can also be worn by itself as a regular safety glass
- Molded nose bridge design to fit the vast majority of users
- Indirect vent temples to reduce fogging
- 4 Base curve lens
- Meets ANSI Z87.1+
-  **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Fits Comfortably Over Personal Eyewear
- General Manufacturing
- Construction Applications
- Indoor Work

Technical Data

Color	Clear
Sizes Available	OS
Packaging	Bagged Each
Packed	144/Case
Case Dimensions (in)	27.95 x 13.78 x 11.81
Case Weight (lbs)	19.84
Country of Origin	Malaysia
Lens	Clear
Frame Style	Over-The-Glass
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Uncoated
Bridge	Molded
Temple	Spatula
Diopter	--
Base Curve	4
Construction	--
Certifications	ANSI Z87.1, CSA Z94.3 Certified
Product Circularity	Recycled via Terracycle

Care Instructions

KEY:  Made from recycled or bio-based  Launderable  Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-22



SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
250-99-0900	Clear	Clear	Clear	AS	616314024771	01616314024771	02616314024771
250-99-0980	Clear	Clear	Clear	U	616314025136	01616314025136	02616314025136
250-99-0980DP	Clear	Clear	Clear	U	616314027598	01616314027598	02616314027598
250-99-0901	Gray	Tinted	Gray	AS	616314025143	01616314025143	02616314025143

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated