




## Traditional Spectacle

Full Frame Safety Glasses with Smoke Frame, Gray Lens and Anti-Scratch Coating

- Classic dual lens style with sturdy propionate frame
- Long lasting heavy-duty metal hinges
- Molded nose bridge design to fit the vast majority of users
- U-Fit® spatula temples with a wire core
- 6 Base curve lens
- Meets ANSI Z87.1+
-  **WARNING:** Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Applications

- Outdoor Work
- Construction Applications
- Public Works



## Technical Data

Color	Smoke
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	21.93 x 11.65 x 12.20
Case Weight (lbs)	10.80
Country of Origin	Taiwan
Lens	Tinted
Frame Style	Full
Lens Color	Gray
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Molded
Temple	Spatula
Diopter	--
Base Curve	6
Construction	--
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

## Care Instructions

KEY:  Made from recycled or bio-based  Launderable  Recyclable via TerraCycle®

**PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-20



## SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
249-5907-207	Smoke	IR Filter	Green	AS/AF	616314102325	01616314102324	02616314102323
249-5907-400	Smoke	Clear	Clear	AS/AF	616314115479	01616314115478	02616314115477
249-5907-401	Smoke	Tinted	Gray	AS/AF	616314115486	01616314115485	02616314115484

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated