



2000 Electrician's Duct Tape

Data Sheet

Product Description

Scotch® 2000 Electrician's Duct Tape is a water resistant duct tape with a polyvinyl chloride (PVC) backing and a rubber adhesive. Scotch 2000 is designed to be an electrician's utility tape for holding and bundling applications.

- Easy tear
- No cloth—does not absorb water.
- Clean removal (minimal residue)
- Not recommended for sealing air ducts.

Typical Data/Physical Properties

Test Method	Typical Value
Color	Gray
Thickness ASTM D-1000	6 mils (.006")
Adhesion to Steel ASTM D-1000	20 oz./in.
Tensile Strength ASTM D-1000	12 lb./in.
Elongation at Break ASTM D-1000	100%

Note: *These are typical properties and should not be used for specification purposes.*

Shelf Life

Scotch 2000 has a three year shelf life (from date of manufacture) when stored under the following recommended storage conditions. Store behind present stock in a clean, dry place at a temperature of 70°F (21°C) and 40-50% relative humidity. Good stock rotation is recommended.

Availability

Scotch 2000 duct tape is available from your local authorized 3M distributor in the following roll size:

2 in. x 50 yds. (51 mm x 46 m)

3M and Scotch are trademarks of 3M.

IMPORTANT NOTICE

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture for a period of 3 years from the date of manufacture. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the shelf life period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**



Electrical Products Division

6801 River Place Blvd.
Austin, TX 78726-9000
800/245-3573
www.3M.com/elpd



*Printed on 50% recycled paper
with 10% post-consumer*

Litho in USA
©3M 1999 78-8124-5503-4-A