



Evolution® Deluxe 6151

Standard Brim, Vented Hard Hat with HDPE Shell, 6-Point Polyester Suspension and Wheel Ratchet Adjustment

- High-Density Polyethylene (HDPE) shell designed with five raised channels running across the top for strength, and an extended back area for extra protection
- 6-Point polyester textile suspension system offers unrivaled comfort without compromising performance
- Unique "3D Adjustment" provides a precise fit using harness depth settings unlike any other hard hat on the US market today
- Revolution™ Wheel Ratchet is easy to use and creates a firm comfortable fit
- Vented to reduce inside helmet temperatures
- Chamlon™ sweatband
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications



Technical Data

Color	Blue, Neon Orange, Neon Yellow, White, Yellow, Gray
Sizes Available	OS
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	23.03 x 9.45 x 17.91
Case Weight (lbs)	11.02
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Chin Strap	--
Sweatband	Chamlon
Construction	--
Certifications	ANSI/ISEA Z89.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type I
CSA Type	--
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-23



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-EV6151V-50	Blue	OS	5038428021449	5038428813228	5038428813228
280-EV6151V-40	Gray	OS	5038428814171		5038428239615
280-EV6151V-OR	Neon Orange	OS	5038428018890	5038428813136	5038428813136
280-EV6151V-LY	Neon Yellow	OS	5038428192217	5038428813785	5038428813785
280-EV6151V-10	White	OS	5038428136815	5038428812030	5038428812030
280-EV6151V-20	Yellow	OS	5038428136822	5038428812047	5038428812047