



LULU

120V PENDANTS

location:
DAMP

SPECIFICATIONS:

DESCRIPTION

Our Lulu is a playful look, inspired by it's purposeful angularity and positioning like the proverbial "puppet on a string" The Foil glass is sparkling and metallic, with a lightly distressed inner surface onto a glossy clear blown glass. This décor is full of texture and depth, however the outer surface of the glass is smooth and clean. When lit the glass comes to life, as the distressed foil allows glimpses of light to pass through. This blown glass is handcrafted by a skilled artisan, utilizing century-old techniques passed down from generation to generation. Each piece of this décor has its own artistic nature that can be individually appreciated.

LAMPING

Standard: 75W A19 120V incandescent, lamp not included. Dimmable with standard incandescent dimmer (not included).

LED Filament: 8W Replaceable A19 LED Filament lamp, 120V, dimmable, 80+ CRI, 3000°K CCT, 800 lumens, 15,000 hours, lamp included.

DIFFUSER

Shade shall be of glass with metallic foil decors. 7.75" L x 8" H

SUSPENSION

Cord-hung: 10' SVT-type cord and a cable support. Jacket coordinates with metal finish. Plated stamped steel construction.

MOUNTING


Installs directly to a 4" octagonal ceiling box. Suitable for sloped ceilings.

LABELS

UL or ETL Listed. Suitable for Damp Locations (interior use only).



LULUCF (COPPER FOIL)



LULUGF
GOLD FOIL

LULUSF
SILVER FOIL



Project Information:

For ordering information, see next page

All dimensions provided are nominal.
Allowance must be made for dimensional tolerance in handcrafted glasses.

REV 5/22




ORDERING:

CONNECTION	SHADE OPTIONS	LAMP OPTIONS	METAL FINISH	OPTIONS
Cable Fixture	LULUCF Copper Foil	(blank) 75W A19 Incan	BK Black	L 15' cord
1JT Flat Canopy	LULUGF Gold Foil	EDIL 8W LED Filament	BR Bronze	LW Low wattage labeling
	LULUSF Silver Foil		SN Satin Nickel	

Ex. 1JT-LULUSF-SN
Lulu Pendant w/ Silver Foil Shade,
Satin Nickel Finish

PENDANT OPTIONS:

1JT MONOPOINT PENDANT CANOPY



- Flat Canopy style with an additional cable support.
- Suitable for sloped ceilings
- Cord: 10' SVT
- Black, Bronze or Satin Nickel

ACCESSORIES:

LONGER CORD LENGTHS:

Longer cord length of 15' available.
Add an "L" to the end of the item number, i.e. 1JT-LULUGF-SNL.

LOW WATTAGE LABELING:

Incandescent fixture supplied with 16 watt relamp label.
Add an "LW" to the end of the item number, i.e. 1JT-LULUSF-SN-LW.