



# TAY TAY

VANITIES WALL

location:  
**DAMP**

## SPECIFICATIONS:

### DESCRIPTION

2-4 light vanity luminaires featuring handcrafted glass.

### LAMPING

**Standard:** 40W Low-pressure G9 Halogen, 120V, lamp included. Suitable for use in an open fixture. Dimmable with standard incandescent dimmer (not included).

**LED:** 5W Replaceable source, 120V, dimmable, 90+ CRI, 3000° K CCT, 450 lumens, 25,000 hours, lamp included.

### DIFFUSER

Shade shall be handcrafted glass of various decors.  
4.125" Dia. x 3.875" H, spaced 7.875" apart on center.

### CONSTRUCTION

Fixture utilizes metal arm assembly and stamped steel body, with plated finish. Decorative finials can be removed for downlighting applications. Decorative outlet box cover optional when not required.

### METAL FINISH

Fixture shall be finished in Bronze, Chrome or Satin Nickel.

### MOUNTING

Installs directly to a 4" octagonal outlet box, with 1.75" left or right offset. Canopy allows direct wiring without outlet box, where armored cable or non-metallic sheathed cable is employed, and the decorative outlet box cover is not required. Orient upward or downward, wall-mount only.

### LABELS

UL or ETL Listed. Suitable for Damp Locations (interior use only).



TAY TAY SHOWN IN CARRERA (560519) IN DOWNWARD ORIENTATION

560507  
OPAL MATE



5605VM  
VANILLA MATTE



560580  
AMBER MATTE



560560  
COCOON



5605HN  
HONEY



560541  
GARNET



560518  
AMBER CLOUD



5605HB  
HABANERO




5605MA  
MAGMA



5605CE  
CEYLON



560586  
BLUE CLOUD



For ordering information, see next page

All dimensions provided are nominal.  
Allowance must be made for dimensional tolerance in handcrafted glasses.




REV 12/18



ORDERING:

FIXTURE	GLASS OPTIONS	METAL FINISH	METAL FINISH	OPTIONS
2SW 2 Light Vanity	560507 Opal Matte	(blank) 40W G9 Hal	BR Bronze	SQ Square Canopy
3SW 3 Light Vanity	560518 Amber Cloud	LED 5W LED 120V, dimmable	CR Chrome	
4SW 4 Light Vanity	560519 Carrera		SN Satin Nickel	
	560541 Garnet			
	560560 Cocoon			
	560580 Amber Matte			
	560586 Blue Cloud			
	5605CE Ceylon			
	5605HB Habanero			
	5605HN Honey			
	5605MA Magma			
	5605VM Vanilla Matte			

**Ex. 3SW-560519-SN**  
 Tay Tay 3-Light Vanity w/ Carrera Glass,  
 Satin Nickel Finish



Canopy allows direct wiring without outlet box, where armored cable or non-metallic sheathed cable is employed, and the decorative outlet box cover is not required. Orient upward or downward, wall-mount only.

**Project Information:**