

Topgard® Protective Caps & Full Brim Hats

Technical Specifications



Made of durable polycarbonate and featuring a uni-ridge design, these caps are designed for use by utilities and other industries where head protection with dielectric protection is necessary.

Topgard cap shown with Fas-Trac® III Suspension



Features

- Superior top impact protection
- Tested to radiant heat loads producing temperatures up to, but not exceeding, 275°F
- Slotted cap designed for use with MSA accessories to ensure compliance with the helmet & accessory

Markets

- Electric/utilities
- Oil, gas and petrochemical
- General industry and manufacturing
- Construction

Customization

- 27+, factory applied reflective or retro-reflective stripes
- Multiple printing services: one-color logo to digital photos; up to four locations
- For additional details, visit msasafety.com KEYWORD: logo

Care & Maintenance

- Clean helmet assembly regularly with MSA's Confidence Plus Cleaning Solution (P/Ns 10009971 or 10032737) or mild soap (no detergents) and warm water
- Do not throw, drop, use as support or abuse helmet to ensure proper working condition
- Store helmet in clean, dry environment <49°C (120°F)

Service Life Guidelines

- Topgard Helmets are made with high-quality, wear-resistant materials
- Inspect the helmet before and after each use and replace any part(s) as required
- Always replace the helmet after it has withstood an impact or penetration. MSA recommends:
 - replacing the suspension after no more than 12 months of use
 - replacing the shell after no more than five (5) years of use
- Please consult user instructions for additional details

Specifications

STANDARDS COMPLIANCE	ANSI/ISEA Z89.1-2014 CSA Z94.1-2014
CLASSIFICATION	Type I, Class E
CERTIFICATION	Third-party by SEI
APPLICATION(S)	General Purpose; Elevated Temperatures
PRODUCT SIZES	Standard (6½" to 8")
SHELL MATERIAL	Polycarbonate with UV inhibitor
AVAILABLE STYLES	Slotted Cap Unslotted Full Brim Hat
AVAILABLE SUSPENSIONS	Fas-Trac® III Ratchet 1-Touch Slide Closure Swing Ratchet
REQUIREMENTS FOR OPTIONAL FEATURES (Z89.1)	Reverse Donning, Lower Temperature, Higher Temperature, Hi-Viz (as indicated)
COLORS	8 (stocked for caps) 4 (stocked for hats) Other colors available, including custom colors
OTHER PPE	MSA accessories (including lamp bracket/cord holder), MSA hearing protectors, V-Gard Face Protection System, Winter Liners and chinstraps
PRODUCT DIMENSIONS	
CAP	11.5" x 8.75" x 5.75", 0.74 lb
HAT	12.25" x 10.75" x 6.25", 0.88 lb
MIN ORDER QUANTITIES (MOQ)	20 (stocked colors) 100 (non-stocked colors) 500 (custom colors)
SHIPPING CARTON DIMENSIONS (BOX OF 20)	
CAP	22.5" x 18.25" x 14", 19.6 lb
HAT	25.1875" x 21.75" x 15.5", 22.4 lb

Technical Assistance/Additional Information

For more information about Topgard Helmets and other MSA products, please contact MSA Customer Service at 1-800-MSA-2222 or visit MSAsafety.com.

MSA – The Safety Company
1000 Cranberry Woods Drive
Cranberry Township, PA 16066 USA
Phone 724-776-8600
www.MSAsafety.com

U.S. Customer Service Center
Phone 1-800-MSA-2222
Fax 1-800-967-0398

MSA Canada
Phone 1-800-672-2222
Fax 1-800-967-0398

ID 0612-08-MC / July 2015

© MSA 2015 Printed in U.S.A.

Because every life has a purpose...