



Technical Data

Color	Hi-Vis Yellow
Sizes Available	S-2XL
Packaging	Bulk Pack
Packed	6 Dozen/Case
Case Dimensions (in)	10.55 x 11.42 x 27.17
Case Weight (lbs)	25.35
Country of Origin	China
Liner Material	PolyKor
Lining	Acrylic
Cuff	Knit Wrist
Coating	Nitrile
Coating Color	Black
Coating Coverage	Full Hand
Grip	Foam
Gauge	15
Construction	Coated Seamless Knit
Certifications	--
Product Circularity	Reusable / Launderable

G-Tek® PolyKor®

Seamless Knit PolyKor® Blend Glove with Acrylic Liner and Double-Dipped Nitrile Foam Grip on Full Hand

- Seamless construction for a comfortable fit
- PolyKor® blended shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Acrylic lined gloves provide economical cold weather protection
- Nitrile foam coating provides superior grip in dry, wet and oily applications
- Fully coated flat nitrile helps keep hands dry in wet applications
- Knit wrist helps prevent dirt and debris from entering the glove

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Medium to Large Parts and Materials
- Metal Fabrication
- Mechanical Equipment Maintenance and Repair
- Heavy to Medium Fastening and Anchoring

Performance Data

ANSI Cut Level (2016)	A3
ANSI Puncture Level	--
EN Abrasion Level	4
EN Cut Level	X
EN Tear Level	3
EN Puncture Level	2

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-04-24



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
41-1415/S	Hi-Vis Yellow	S	616314206979	01616314206978	02616314206977
41-1415/M	Hi-Vis Yellow	M	616314206962	01616314206961	02616314206960
41-1415/L	Hi-Vis Yellow	L	616314206955	01616314206954	02616314206953
41-1415/XL	Hi-Vis Yellow	XL	616314206986	01616314206985	02616314206984
41-1415/XXL	Hi-Vis Yellow	2XL	616314263040	01616314263049	02616314263048