

HONEYWELL UVEX BIONIC[®] SHIELD

The face shield workers want to wear.



Honeywell
UVEX[®]

HONEYWELL UVEX BIONIC® SHIELD

The Honeywell Uvex Bionic is a revolutionary face shield. Designed for rugged jobs, it's tough where it has to be, yet extremely lightweight and balanced for all-day comfort. Its technologically advanced design enables the Bionic to more easily stand up to airborne debris, splash and welding infrared radiation. Highly adjustable, with an easily replaceable visor, Bionic is the face shield workers want to wear.

SUPERIOR PROTECTION

- Full shield design provides built-in chin protection and
- Extended top-of-head coverage for enhanced protection from airborne debris
- Perfect for workers exposed to falling or flying objects, impact, chemical splash, and airborne debris¹
- Excellent optics provide increased visibility
- 100% dielectric — no metal parts
- Meets ANSI Z87.1-2015 (High Impact)
- CSA Z94.3 certified

ULTIMATE COMFORT

- Lightweight, balanced, ergonomic design for extended use
- Dual position headgear provides a customizable fit
- Comfortable cell foam on back of headgear
- Breathable, removable, washable headband
- Comfortably worn with most goggles and respirators
- 2,784 possible adjustment positions

COST-OF-OWNERSHIP VALUE

- Easily replaceable visor allows for multiple visor tints and extends the life of the shield
- Hard hat accessory (dielectric) expands face shield use and is compatible with major hard hat manufacturers' styles



Highly adjustable headgear tilts visor nearer or farther from face depending on preference and application.



Easy-to-set, ratcheting headgear locking mechanism assures comfortable, secure fit.



Shell offers built-in chin protection and extended top-of-head coverage.



Comfortable cell foam on back of headgear.

¹) Face shield offers secondary protection and MUST be worn with certified safety eyewear.



Face Shield
SKU: S8500



Hard Hat Adapter Accessory
SKU: S8515



Clear

Ideal for most indoor work applications



Shade 3.0

Infra-dura® Welding shade for
torch brazing operations



Shade 5.0

Infra-dura® Welding shade
for cutting operations

ORDERING INFORMATION

ITEM #	DESCRIPTION	VISOR	COATINGS
FACE SHIELD			
S8500	Face Shield	Clear PC	Uncoated
S8505	Face Shield and Hard Hat Adapter (no suspension)	Clear PC	Uncoated
S8510	Face Shield	Clear PC	Hard Coat / Anti-fog
S8515	Face Shield and Hard Hat Adapter (no suspension)	Clear PC	Hard Coat / Anti-fog
REPLACEMENT VISORS			
S8550	Replacement Visor	Clear PC	Uncoated
S8555	Replacement Visor	Clear PC	Hard Coat / Anti-fog
S8560	Replacement Visor	Shade 3.0	Uncoated
S8565	Replacement Visor	Shade 5.0	Uncoated
ACCESSORIES			
S8580	Sweatband	-	-
S8590	Hard Hat Adapter	-	-
S8595	Bionic Ratchet Suspension	-	-

Package Information
Face Shield
Ind. Box, 4/Master Case

Package Information
Replacement Visors
Ind. Polybag, 10/Master Case

For more information

sps.honeywell.com

Technical Service: 800.873.5242

Honeywell Personal Protective Equipment

300 S Tryon St Suite 500
Charlotte, NC 28202

US: Canada:
Tel. 800.430.5490 Tel. 888.212.7233
Fax. 800.322.1330 Fax. 888.667.8477

Honeywell Uvex Bionic® Brochure | 03/21
© 2021 Honeywell International Inc.

