

New!

MILLER® FALCON™

WEB SELF-RETRACTING LIFELINE

**16-ft. & 20-ft.
Models Available**

Introducing the newest addition to the lightest, most rugged line of composite retractables on the market.

- **Lightest, most compact web self-retracting lifeline**
- **Offers Xtreme durability with a strong, composite housing**
- **High-strength Technora® webbing provides extreme durability**
- **Load indicator for greater safety**
- **Swivel at the top of unit to prevent lifeline from twisting during use**
- **Rated for up to 400 lb. (181kg) worker**
- **Units are repairable and require no annual factory recertification** -- lowers cost of ownership**


** Except in Canada where the Canadian Standards Association requires annual factory recertification.

MILLER®

by Honeywell



Dimensions:



SPECIFICATIONS

MATERIALS

Housing:	High impact-resistant nylon
Hub:	Aluminum and high-strength composite
Braking Mechanism:	High-strength steel, yellow zinc chromate plating
Lifeline:	Width: .69-in. (17.5mm) Core: Technora® (aramid fiber) Outer cover: Chemically-treated polyester for increased abrasion resistance
Snap Hook:	Aluminum: (MP16P/16FT & MP20P/20FT) Steel: (MP16P-Z7/16FT & MP20P-Z7/20FT)
Carabiner:	Aluminum: (MP16P/16FT & MP20P/20FT) Steel: (MP16P-Z7/16FT & MP20P-Z7/20FT)


TECHNICAL

Maximum Working Load:	Up to 400 lbs. (181kg)
Working Length Capacity:	16 ft. (4.9m) or 20 ft. (6.1m)
Maximum Arresting Force:	<900 lbf. (4kn) for up to 310 lbs. (141kg) Working Load <1800 lbf. (8kn) for up to 400 lbs. (181kg) Working Load

Meets all applicable OSHA, ANSI*, CSA and CE requirements.

Model	Description	Weight
MP16P/16FT	Miller Falcon 16-ft. (4.9m) web lifeline with stainless steel swivel, aluminum carabiner and aluminum snap hook	3.5 lbs. (1.59kg)
MP20P/20FT	Miller Falcon 20-ft. (6.1m) web lifeline with stainless steel swivel, aluminum carabiner and aluminum snap hook	3.6 lbs. (1.63kg)
MP16P-Z7/16FT*	Miller Falcon 16-ft. (4.9m) web lifeline with stainless steel swivel, steel carabiner and steel snap hook	4.1 lbs. (1.86kg)
MP20P-Z7/20FT*	Miller Falcon 20-ft. (6.1m) web lifeline with stainless steel swivel, steel carabiner and steel snap hook	4.2 lbs. (1.90kg)

*ANSI Z359-2007 compliant for connectors which meet the 3,600 lbs. gate requirements.



The complete line of Miller Falcon Self-Retracting Lifelines includes galvanized or stainless steel wire rope units.

Nearly indestructible, high impact-resistant nylon housing withstands the harsh rigors of the toughest applications. Pound for pound the strongest, most durable line of self-retracting lifelines on the market. Lifeline available in 20- (6.1m), 30- (9.1m), 50- (15m) and 65-ft. (20m) lengths. In addition, models are available as ANSI Z359-2007 compliant.



MP20G/20FT



MP50G/50FT

This equipment should only be used after reading the manufacturer's instructions. Failure to follow instructions could result in serious injury or fatality.



by Honeywell

Ask the Expert ... Ask Miller.

800/873-5242
or 814/432-2118

Fax 800/892-4078
or Fax 814/432-2415

www.millerfallprotection.com

For more information or to place an order, please contact your Miller® distributor:

LMFWSRL/0607/20M/RPI