



Rocky™

Industrial Climbing Helmet with Polycarbonate / ABS Shell, Hi-Density Foam Impact Liner, Nylon Suspension, Wheel Ratchet Adjustment and 4-Point Chin Strap

- Ultra lightweight shell made with Polycarbonate / ABS material provides superior protection
- 4-point quick release suspension with dual position height adjustment ensures a proper fit
- Strong double-layer woven nylon straps provide durability and secure fit for all day wear
- Inner suspension includes comfortable padding for above the brow line, crown and back of head
- Rugged non-slip adjustable SURE-LOCK wheel ratchet ensures proper suspension performance and effortless fit for all head sizes
- Universal accessory slots accommodate eye, face and hearing protection

Applications

- Working at Heights
- Wind Energy
- Scaffolding
- Telecom
- Utility Work



Technical Data

Color	Black, Gray, Light Blue, Orange, Red, White, Yellow, Green
Sizes Available	OS
Packaging	Boxed
Packed	8/Case
Case Dimensions (in)	17.50 x 12.50 x 24.50
Case Weight (lbs)	6.39
Country of Origin	Canada
Shell Material	ABS / Polycarbonate
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Micro
Size Adjustment	Wheel Ratchet
Suspension	4 Point Nylon Webbing Cradle
Chin Strap	4-Point Polyester
Sweatband	Felt Lined Foam
Construction	--
Certifications	CSA Z94.3 Certified, ANSI/ISEA Z89.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type II
CSA Type	--
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-23



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP142R-11	Black	OS	620606003399	10620606003396	10620606003396
280-HP142R-09	Gray	OS	620606003382	10620606003389	10620606003389
280-HP142R-04	Green	OS	620606003368	10620606003365	10620606003365
280-HP142R-06	Light Blue	OS	620606003375	10620606003372	10620606003372
280-HP142R-03	Orange	OS	620606003351	10620606003358	10620606003358
280-HP142R-15	Red	OS	620606003405	10620606003402	10620606003402
280-HP142R-01	White	OS	620606003337	10620606003334	10620606003334
280-HP142R-02	Yellow	OS	620606003344	10620606003341	10620606003341