




G-Tek® PolyKor® X7™

Seamless Knit PolyKor® X7™ Blended Glove with NeoFoam® Coated Palm & Fingers - Touchscreen Compatible

- Seamless construction offers increased comfort and breathability
- PolyKor™ blended shell with X7™ technology is super light-weight and thin, offering exceptional cut resistance and durability in a thin liner configuration
- NeoFoam® offers an incredibly secure grip in dry conditions, a versatile and flexible coating that provides breathability and a high degree of dexterity, ideal for handling and the assembly of parts
- Reinforced thumb crotch for extended glove life, enhanced comfort, increased abrasion resistance and added durability in a high-wear area
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves
- Color coded hems for easy size identification

Applications

- Secure Dry and Flexible Grip
- Handling, Assembly and Sorting of Small to Medium Parts and Materials
- Shipping, Receiving and Packaging
- Maintenance and Repair Operations



Technical Data

Color	Burgundy
Sizes Available	XS-2XL
Packaging	Pair Bagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	14.96 x 12.20 x 10.63
Case Weight (lbs)	9.48
Country of Origin	China
Liner Material	PolyKor X7
Coating	Neofoam
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Foam
Gauge	18
Cuff	Knit Wrist
Impact Protection	--
Construction	Coated Seamless Knit, Reinforced Thumb Crotch, Touchscreen Compatible
Certifications	Silicone Free, EN 16350
Product Circularity	Reusable / Launderable Recycled via Terracycle

Performance Data

ANSI Cut Level (2016)	A3
ANSI Abrasion Level	4
ANSI Puncture Level	2
ANSI Impact Level	--
ANSI Contact Heat Level	--
EN 388	4X31CX
ASTM F1358 Vertical Flame Level	--
EN 407	--

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-23



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
16-368/XS	Burgundy	XS	616314692567	10616314692564	20616314692561
16-368/S	Burgundy	S	616314249891	01616314249890	02616314249899
16-368/M	Burgundy	M	616314249907	01616314249906	02616314249905
16-368/L	Burgundy	L	616314249914	01616314249913	02616314249912
16-368/XL	Burgundy	XL	616314249921	01616314249920	02616314249929
16-368/XXL	Burgundy	2XL	616314249938	01616314249937	02616314249936