


HICFM

OWNER'S MANUAL

20" HIGH-VELOLITY PEDESTAL FAN



ITEM NO.: FAN-P20W

120V / 60Hz, 1.35A

READ & SAVE THESE INSTRUCTIONS

Questions, problems, missing parts? Before returning the product,

please e-mail our customer service by

hicfm@outlook.com

SAFETY INFORMATION


WARNING

1. Read and save these instructions. Do not operate fan unless you have read these instructions.
2. Unplug the fan before moving it or performing maintenance. Do not touch the fan when your hands are wet.
3. Those who are not qualified electricians should not disassemble, repair or rebuild the fan.
4. Unplug the fan when it is not in use.
5. DO NOT unplug the fan by pulling the cable cord. Unplug by holding the plug and pulling.
6. DO NOT use the fan when there is damage to the cable cord or plug. If the supply cord is damaged, it has to be replaced by the manufacturer, its service agent or similarly qualified persons.
7. To Reduce The Risk Of Fire, Electric Shock Or Injury To Persons, Do Not Use Replacement Parts That Have Not Been Recommended By The Manufacturer (e.g. Parts Made At Home Using A 3D Printer).
8. DO NOT use the fan close to fires.
9. DO NOT insert your hand or other objects into the grille or the movable parts.
10. To reduce the risk of fire or electric shock, do not use this fan with any solid-state speed control device.
11. DO NOT use this fan outdoors, this fan is designed for indoor use only.
12. To Reduce The Risk Of Fire Or Electric Shock Do Not Use With An Extension Cord.

CAUTION

1. Unplug the fan from the socket and clean it with a soft cloth.
2. DO NOT immerse the fan.
3. Fit the guard onto fan before starting up the fan.
4. This fan is not intended for use by people (including children) with reduced physical, sensory or mental capabilities or lack of experience and knowledge unless they have been given supervision or instruction concerning use of the fan by a person responsible for their safety. Supervise children to ensure they do not play with the fan.

PACKAGE CONTENTS




Part	Description	Quantity
A	Fan head	1
B	Standing pole	1
C	Base	1

ASSEMBLY INSTRUCTION


1 Extending the standing pole

- Loosen the height adapter (1) on the standing pole (B). Then pull the upper portion of the standing pole (B) to the desired height and re-tighten the height adapter (1).




2 Removing hardware from the standing pole

- Remove the triangular knob (BB) and washer (AA) from the standing pole (B). Retain the triangular knob (BB) and washer (AA) for future use.




3 Attaching the standing pole to the base

- Attach the standing pole (B) to the base (C) using the triangular knob (BB) and washer (AA).



4 Attaching the fan head


- Place the fan head (A) on top of the standing pole (B) and secure in place using the plum knob (CC).



OPERATION INSTRUCTION


1 Adjusting the fan tilt angle

- Ensure the fan is unplugged from the power source before adjusting the height or angle.
- Place the fan on a safe, flat surface where it cannot fall or be pulled by the cord.
- To adjust the angle of the fan head (A), loosen the fan head knob (2), tilt the fan head (A) to the desired angle, and re-tighten the fan head knob (2).



2 Turning the fan On/Off and adjusting the airflow settings

- Plug the power cord into an outlet.
- Turn the switch to the desired speed. The settings are 0 = off, 1 = Low, 2 = Medium, 3 = High.
- Turn the oscillation function on by pressing the oscillation button down. Turn the oscillation function off by pulling the oscillation button up. Always turn off and unplug the fan after using.



CARE AND MAINTENANCE


Unplug the appliance before cleaning. Don't use any water for cleaning metal surfaces. Slightly moisten a cloth and then wipe off the surfaces of the fan. In order to remove dust from the grill, use a vacuum cleaner or remove the front grill by removing the securing screws on the edge of the grill. After cleaning, remount the grill. After doing this, fasten the screws on the edge of the grill.

1-YEAR LIMITED WARRANTY

The manufacturer warrants this product to be free from manufacturing defects in the material and workmanship under normal use for a period of one year after the date of purchase by the original purchaser.

This warranty does not cover transit damages. This warranty does not apply to damages from accident, misuse, alteration of any kind to the fan or where the connected voltage is more than above the nameplate voltage. This warranty does not apply to the finish on any portion of the product. Servicing performed by unauthorized persons shall render the warranty invalid. The warranty is not responsible for damages of any kind, including accident and consequential damages. Some states do not allow the exclusion or limitation of the incidental or consequential damages, so the above exclusion or limitation may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

REPLACEMENT PARTS LIST



PART	DESCRIPTION	PART #
1	Blades	FAN-P20W