

## 4-11/16" SQUARE (5S) ADJUSTABLE RINGS

### PRODUCT FEATURES

- ▶ For use with 4-11/16" Square (5S) 2-1/8" or deeper boxes
- ▶ 1/4" to 1-1/4" adjustability range
- ▶ Rings achieve a flush finish every time
- ▶ Compatible with exclusive extensions for infinite wall depths

### U.S. PATENT NO.:

7,468,486



**Video Available  
On Our Website!**

Cat. No.	Description	Standard	With One Extension Installed		Std. Pkg.
			+ 1GX75	+ 2GX75	
5SAR1G	1-Gang Adjustable Ring for 4-11/16" Sq. Deep Boxes	1/4" to 1-1/4"	1" to 2"	-	25
5SAR2G	2-Gang Adjustable Ring for 4-11/16" Sq. Deep Boxes	1/4" to 1-1/4"	-	1" to 2"	25



5SAR1G



5SAR2G



### ACCESSIBLE ADJUSTABILITY

Corner screws are easily accessible for adjustment before and after the device has been installed

## EXTENSIONS AND ACCESSORIES

### PRODUCT FEATURES

- ▶ Extensions ensure flush finish regardless of wall thickness
- ▶ Attach to adjustable ring for additional 3/4" of depth
- ▶ Mount easily to ring with two 8-32 screws
- ▶ Multiple extensions can be installed on one ring

### U.S. PATENT NO.:

7,468,486

Cat. No.	Description	For Use With	Std. Pkg.
1GX75	1-Gang 3/4" Extension	4SAR1G, 5SAR1G, or WBAR1G Only	50
2GX75	2-Gang 3/4" Extension	4SAR2G, 5SAR2G, or WBAR2G Only	50
UPC	Gangable, Steel Universal Protective Cover protects any device during drywall, painting, routing, mudding & plastering		25
UPCTS	Optional Plastic Insert for UPC to protect Toggle Switch		25



1GX75




2GX75



UPC



UPCTS



Exploded View



Complete UPC Assembly Shown  
Installed with Toggle Switch

## STUD MOUNTING ADJUSTABLE RINGS


### PRODUCT FEATURES

- ▶ Accepts 4" or 4-11/16" square boxes in line voltage applications
- ▶ Mount to any stud, shear wall, 6" X 6" NEMA 1 enclosure, Simple Support Bracket (Pg. P1) or Ultimate Support Bracket (Pg. P5)
- ▶ Can be used standalone for low voltage communications applications


### U.S. PATENT NO.:

7,468,486

Cat. No.	Description	Standard	With One Extension Installed		Std. Pkg.
			+ 1GX75	+ 2GX75	
WBAR1G	1-Gang Universal Box Bracket	1/4" to 1-1/4"	1" to 2"	-	25
WBAR2G	2-Gang Universal Box Bracket	1/4" to 1-1/4"	-	1" to 2"	25



WBAR1G



WBAR2G



WBAR on the 6" x 6" NEMA Enclosure